# This data sheet is the property of Rosenberger North America Akron, LLC. By acceptance of this document, you agree that all the rights to drawings, specifications, processes, and other data therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberger North America Akron, LLC, and are disclosed in confidence. They are not to be manufactured, used, sold, or disclosed to others, no rare devices embodying such features or information derived from these disclosures to be used or disclosed unless and until expressly authorized by Rosenberger North America Akron, LLC. These drawings, specifications, processes, etc., are and remain the property of Rosenberger North

## Rosenberger **Technical Data Sheet** Male Full Detent **WSMP** W1S103-40ML5 Right Angle Launch WSMP MALE FULL 2X Ø .095 [2,41] **DETENT INTERFACE** $.023 \pm .003$ $[0,58\pm0,07]$ R/P .098 [2,49]Ø.0090 [0,23].049 [1,24] $.0675 \pm .0050$ $[1,71\pm0,12]$ .045 [1,14] MAX All dimensions are in inches [mm] Interface According to Rosenberger WSMP™ Interface standards Material and plating **Plating Connector parts Material Body and Contact** Kovar® per ASTM F15 Hard gold 6µIN [0,15µm] min, over Nickel, 80µIN [2,0µm] min Dielectric 7070 Glass

Rosenberger North America Akron, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com

Tel. : +1.717.859.8900 : +1.717.859.7044 Page

1/2

FR-053 RNA Datasheet2 Rev A 08/01/2022

# rdata therein, as well as the proprietary and novel features of the subject matter, are reserved by Rosenberger North America Akron, LLC, and are disclosed in confidence. They not to be manufactured, used, sold, or disclosed to others, nor are devices embodying such features or information derived from these disclosures to be used or disclosed unless and it is a semberger North America Akron, LLC, These drawings, specifications, processes, etc., are and remain the property of Rosenberger North America Akron, LLC, These drawings, specifications, processes, etc., are and remain the property of Rosenberger North and the property of Rosenberger North America Akron, LLC, and are not to be copied or reproduced without permission. This data sheet i other data therei are not to be n and until expre America Akror

### **Technical Data Sheet**

# Rosenberger

**WSMP** 

Male Full Detent Right Angle Launch

W1S103-40ML5

# Electrical data (@ STP unless otherwise specified)

Impedance  $50 \Omega$ 

Frequency DC to 65 GHz

Return loss  $\geq$  26 dB, DC to 26 GHz  $\geq$  19 dB, 26 to 40 GHz

 $\geq$  14 dB, 40 to 50 GHz < 0.12 x  $\sqrt{f(GHz)}$  dB

Insertion loss  $\leq 0.12 \text{ x } \sqrt{f(GHz)} \text{ dB}$ Insulation resistance  $\geq 3.5 \text{ x} 10^3 \text{ M}\Omega$ 

 $\begin{array}{lll} & = 3.0 \text{ M} \\ & = 3.0 \text{ m} \\ & \leq 2.0 \text{ m} \\ & \\ & \text{Outer contact resistance} \\ & & \leq 6.0 \text{ m} \\ & \\ & \text{Test voltage} \\ & &$ 

RF High Potential 150 V rms @ 5 MHz

RF-leakage ≥ -80 dB (typical mated pair)

### Mechanical data

Mating cycles

Full Detent ≥ 100

**Engagement force** 

Full Detent 2.5 lb<sub>f</sub> [11 N]

Disengagement force

Full Detent 4.5 lb<sub>f</sub> [20 N]

### **Environmental data**

Temperature range -55°C to +165°C

Thermal shock MIL-STD-202 – 107, Condition B

Corrosion MIL-STD-202 – 101

Vibration MIL-STD-202 – 204, Condition D
Shock MIL-STD-202 – 213, Condition I
Moisture resistance MIL-STD-202 – 106, except Step 7B

Max soldering temperature IEC 61760-1, +500°F [+260°C] for 10 seconds

2002/95/EC (RoHS) compliant

Draft	Date	Approved	Date		Rev.	Engineering change number	Name	Date
R. Fisher	6/30/16	R. Hosler	6/30/16		a02	Revised per ECN 23-1039	J. Havener	7/6/2023
Rosenberger North America Akron, LLC					Tel.	: +1.717.859.8900		Page

Rosenberger North America Akron, LLC P.O. Box 309 Akron, PA USA 17501 www.rosenbergerna.com

Fax : +1.717.859.7044 Email : info@rosenbergerna.com

2/2

<sup>\*</sup>Connector only, return loss in application depends decisively on PCB layout