

1.6x0.8x0.5mm BI-COLOR SURFACE MOUNT LED

Features

• 1.6mm X 0.8mm SMD LED

• Package height: 0.5mm

• IR-reflow compatible

Standard Package: 2,000pcs/ Reel
MSL (Moisture Sensitivity Level): 3

• RoHS compliant








ATTENTION

OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
DISCHARGE
SENSITIVE
DEVICES



Absolute Maximum Ratings (T _A =25°C)		Yellow (AlGaInP)	Red (AlGaInP)	Unit
Reverse Voltage	V_{R}	5	5	V
Forward Current	I_{F}	30	30	mA
Forward Current (Peak) 1/10 Duty Cycle 0.1ms Pulse Width	ifs	175	185	mA
Power Dissipation	P_D	75	75	mW
Operating Temperature	$T_{\rm A}$	-40 ~ +85		°C
Storage Temperature	Tstg	-40 ~ +85		

A Relative Humidity between 40% and 60% is recommended in ESD-protected work areas to reduce static build up during assembly process (Reference JEDEC/JESD625-A and JEDEC/J-STD-033)

Operating Characteristics $(T_A=25^{\circ}C)$		Yellow (AlGaInP)	Red (AlGaInP)	Unit
Forward Voltage (Typ.) (I _F =20mA)	V_{F}	2	1.95	V
Forward Voltage (Max.) (I _F =20mA)	V_{F}	2.5	2.5	V
Reverse Current (Max.) $(V_R=5V)$	I_R	10	10	μA
Wavelength of Peak Emission CIE127-2007* (Typ.) (I _F =20mA)	λΡ	590*	645*	nm
Wavelength of Dominant Emission CIE127-2007* (Typ.) (I _F =20mA)	λD	590*	630*	nm
Spectral Line Full Width At Half-Maximum (Typ.) (I _F =20mA)	Δλ	20	28	nm
Capacitance (Typ.) $(V_F=0V, f=1MHz)$	С	20	35	pF


Part Number	Emitting Color	Emitting Material	Lens-color	Luminous Intensity CIE127-2007* $(I_F=20 \text{mA}) \text{ mcd}$		Wavelength CIE127-2007* nm λP	Viewing Angle 20 1/2
				min.	typ.		
XZMYKMDK53W-9	Yellow	AlGaInP	Water Clear	80 80*	148 148*	590*	130°
	Red	AlGaInP		120 40*	248 89*	645*	

^{*}Luminous intensity value and wavelength are in accordance with CIE127-2007 standards.

Feb 25,2019


XDSB5077 V3-X Layout: Maggie L.





Relative Intensity Vs. CIE Wavelength


Wavelength (nm)





 $1.6 \mathrm{x} 0.8 \mathrm{x} 0.5 \mathrm{mm} \; \mathrm{BI\text{-}COLOR} \; \mathrm{SURFACE} \; \mathrm{MOUNT} \; \mathrm{LED}$


Spatial Distribution

❖ Yellow













❖ Red














LED is recommended for reflow soldering and soldering profile is shown below.

Reflow Soldering Profile for SMD Products (Pb-Free Components)




- 1. All temperatures refer to the center of the package, measured on the package body surface facing up during reflow.


 2. Do not apply any stress to the LED during high temperature conditions.

 3. Maximum number of soldering passes: 2


❖ The device has a single mounting surface. The device must be mounted according to the specifications.




❖ Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



❖ Tape Specification (Units:mm)



Reel Dimension



Remarks:


If special sorting is required (e.g. binning based on forward voltage, Luminous intensity / luminous flux, or wavelength), the typical accuracy of the sorting process is as follows:


- 1. Wavelength: +/-1nm
- 2. Luminous intensity / luminous flux: +/-15%
- 3. Forward Voltage: +/-0.1V


Note: Accuracy may depend on the sorting parameters.



PACKING & LABEL SPECIFICATIONS







TERMS OF USE

- 1. Data presented in this document reflect statistical figures and should be treated as technical reference only.
- 2. Contents within this document are subject to improvement and enhancement changes without notice.
- 3. The product(s) in this document are designed to be operated within the electrical and environmental specifications indicated on the datasheet. User accepts full risk and responsibility when operating the product(s) beyond their intended specifications.
- 4. The product(s) described in this document are intended for electronic applications in which a person's life is not reliant upon the LED. Please consult with a SunLED representative for special applications where the LED may have a direct impact on a person's life.
- 5. The contents within this document may not be altered without prior consent by SunLED.
- 6. Additional technical notes are available at https://www.SunLEDusa.com/TechnicalNotes.asp

Feb 25,2019 XDSB5077 V3-X Layout: Maggie L.