

iW7038

16-Channel Internal Current Sink LED Backlighting Driver for HDR LCD TV/Monitor/Notebook Displays

General Description

The iW7038 is a 16-channel, internal current sink, high precision, LED backlighting driver for high dynamic range (HDR) LCD TVs, monitors and notebook displays.

It combines adaptive DC/DC or AC/DC feedback control together with Dialog's patented *BroadLED***[™]** digital adaptive switch mode technology to enable the best system efficiency and thermal performance.

The iW7038 also offers Dialog's **AnyMode™** comprehensive dimming control, which includes head/tail/center mode PWM alignments to reduce motion blur. Additionally, it supports 13-bit PWM dimming and 11-bit analog dimming to improve contrast ratio in HDR applications.

Full protections are included, including built-in LED open/short detection and protection during both start-up and normal operation.

Key Features

- 16 channel LED driver
- Internal current sink MOSFETs
- External current sense resisters
- Single power supply, 12V (9V to 16V range) 50V max. output voltage
- 200mA x 100% duty x 16ch output current capability, support 2 channel grouping
- 13-bit max PWM dimming
 - □ range from 0% to 99.9%
 - \Box 1µs min. PWM output pulse
 - Programmable output slew rate for EMI control (0.35μs/0.70μs/1μs)
- Enhanced pure digital *BroadLED*[™] mode
- 11-bit global or 9 bit independent analog dimming
- LED current and PWM duty update both synchronized to VSYNC
- 46Hz to 32kHz VSYNC input, 46Hz to 32KHz PWM output

- Adaptive external DC/DC or AC/DC feedback control to optimize system power efficiency
- PWM-generator clock
 - HSYNC (up to 22MHz)
 - □ PLL (20MHz)
 - □ Internal OSC (10MHz)
- 16MHz Max SPI with Daisy chain
- Optional Key registers write protection with password, and optional data packet CRC/checksum for noisy SPI interface Programmable LED open/short detection threshold and protection
- High temperature shutdown and auto recovery
- Fault interrupt output (open drain, need external pull up)
- HBM +/- 2kV JESD22-A114 -20 at all pins
- -20 to +85°C operating ambient temperature range
- 145°C max. operating junction temperature
- Package: 7mm x 7mm QFN48 with EP, 0.5mm pin pitch

Applications

- HDR LCD TV
- HDR LCD Monitor

- HDR NB display
- Automobile Display

© 2018 Dialog Semiconductor



System Diagram



Figure 1.1: System Diagram

iW7038



16-Channel Internal Current Sink LED Backlighting Driver for HDR LCD TV/Monitor/Notebook Displays

Pinout



Figure 1.2: Connection Diagram

Table 1: Pin Description

Pin #	Pin Name	Type (Table 2)	Description
1	VIN	AI	Power supply. Connect 4.7µF capacitor to AVSS.
2	AVSS	GND	GND.
3	VDD5	AIO	5V LDO compensation Pin.
			Need a $\ge 4.7 \mu$ F ceramic cap for decoupling. Recommended ESR range of 50m Ω to 350m Ω .
4	FB	AIO	Analog DAC output interface with external AC/DC or DC/DC converter for LED strings.
5	EN	DI	Chip enable.
6	CLKIN/CPLL	DI/AI	PLL compensation input/External clock in.
7	VSYNC	DI	VSYNC clock input in SPI dimming mode
8	FAULTB	DO	Fault status (Active Low) - Open drain.
9	CSB	DI	chip select input for SPI slave . Active LOW.

Product Summary



iW7038

16-Channel Internal Current Sink LED Backlighting Driver for HDR LCD TV/Monitor/Notebook Displays

Pin #	Pin Name	Type (Table 2)	Description	
10	MOSI	DI	Master output, slave input for SPI.	
11	SCK	DI	Serial clock input for SPI.	
12	MISO	DO	Master input, slave output for SPI.	
13	DVSS	GND	GND.	
14	LED16	AI	LED cathode connection for string 16.	
15	S16	AO	Source of internal MOSFET, connect to sense resis	
16	S15	AO	Source of internal MOSFET, connect to sense resistor	
17	LED15	AI	LED cathode connection for string 15.	
18	LED14	AI	LED cathode connection for string 14.	
19	S14	AO	Source of internal MOSFET, connect to sense resistor	
20	S13	AO	Source of internal MOSFET, connect to sense resistor	
21	LED13	AI	LED cathode connection for string 13.	
22	S12	AO	Source of internal MOSFET, connect to sense resistor	
23	LED12	AI	LED cathode connection for string 12.	
24	LED11	AI	LED cathode connection for string 11.	
25	EXPGND	GND	Exposed PAD for LED driver, connect to GND.	
26	S11	AO	Source of internal MOSFET, connect to sense resistor	
27	LED10	AI	LED cathode connection for string 10.	
28	S10	AO	Source of internal MOSFET, connect to sense resisto	
29	S9	AO	Source of internal MOSFET, connect to sense resis	
30	LED9	AI	LED cathode connection for string 9.	
31	LED8	AI	LED cathode connection for string 8.	
32	S8	AO	Source of internal MOSFET, connect to sense resistor	
33	S7	AO	Source of internal MOSFET, connect to sense resistor	
34	LED7	AI	LED cathode connection for string 7.	
35	S6	AO	Source of internal MOSFET, connect to sense resistor	
36	EXPGND	GND	Exposed PAD for LED driver, connect to GND.	
37	EXPGND	GND	Exposed PAD for LED driver, connect to GND.	
38	LED6	AI	LED cathode connection for string 6.	
39	LED5	AI	LED cathode connection for string 5.	
40	S5	AO	Source of internal MOSFET, connect to sense resistor	
41	LED4	AI	LED cathode connection for string 4.	
42	S4	AO	Source of internal MOSFET, connect to sense resistor	
43	S3	AO	Source of internal MOSFET, connect to sense resistor	
44	LED3	AI	LED cathode connection for string 3.	
45	LED2	AI	LED cathode connection for string 2.	
46	S2	AO	Source of internal MOSFET, connect to sense resistor	
47	S1	AO	Source of internal MOSFET, connect to sense resistor	



Table 2: Pin Type Definition

Pin type	Description	Pin type	Description
DI	Digital Input	AI	Analog Input
DO	Digital Output	AO	Analog Output
DIO	Digital Input/Output	AIO	Analog Input/Output

1. Absolute Maximum Ratings

Table 3: Absolute Maximum Ratings

Symbol	Parameter	Min	Max	Unit
VIN	VIN supply voltage	-0.3	20	V
VDD5	5V LDO output	-0.3	7	V
GND pins (AVSS, DVSS, EXPGND)	Ground pins	-0.3	0.3	V
LEDn(LED1~LED16)	LEDn pin voltage	-0.3	50	V
Sn(S1~S16)	Internal MOSFET source pins	-0.3	7	V
Other low voltage pins (CSB, SCK, MISO, MOSI, VSYNC, CLKIN/CPLL, EN, FAULTB, FB)	Digital logic I/O pins and voltage feedback pins	-0.3	7	V
Maximum Operating Junction temperature		-40	150	°C
Storage temperature		-40	150	°C
Latch-up current	h-up current JESD78D		+100	mA
ESD level JEDEC JESD22-A114 - HBM		-2000	+2000	V

Note 1 Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, so functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

5 of 7



2. Package Information



	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.80	0.85	0.90	0.031	0.033	0.035
A1	0.00	0.035	0.05	0.000	0.001	0.002
A2	0.60	0.65	0.67	0.024	0.026	0.026
A3	0.203 REF				0.008 RE	
b	0.20	0.25	0.30	0.008	0.010	0.012
D	6.90	7.00	7.10	0.272	0.276	0.280
D2	5.60	5.75	5.90	0.220	0.026	0.232
Е	6.90	7.00	7.10	0.272	0.276	0.280
E2	5.60	5.75	5.90	0.220	0.226	0.232
е	0.50 BSC			0.020 BSC		
L	0.30	0.40	0.50	0.012	0.016	0.020
	Tolerances of Form and Position					
aaa	0.10			0.004		
bbb	0.10			0.004		
ссс	0.08			0.003		

Controlling dimensions are in millimeters; inch dimensions are for reference only.

Package warpage max. 0.08mm.

Package is IPC/JEDEC Std 020D Moisture Sensitivity Level 3.

This product is RoHS compliant and Halide free.

Compliant to JEDEC Standard MO-220.

Figure 2.1: 48-Lead 7mm x 7mm QFN Package Outline Drawing

48-Lead QFN Package (7mm x 7mm)

-A1

-0.10mm

SEATING PLANE

3. Ordering Information

Part Number	Package	Description	
iW7038-00-QFN4	QFN-7mm x 7mm 48L	Tape & Reel ¹	

Note 1 Tape & Reel packing quantity is 4,000/reel. Minimum ordering quantity is 4,000.

Prod	luct	Sum	mary
	aut	oun	i i i ai y



Disclaimer

Information in this document is believed to be accurate and reliable. However, Dialog Semiconductor does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information. Dialog Semiconductor furthermore takes no responsibility whatsoever for the content in this document if provided by any information source outside of Dialog Semiconductor.

Dialog Semiconductor reserves the right to change without notice the information published in this document, including without limitation the specification and the design of the related semiconductor products, software and applications.

Applications, software, and semiconductor products described in this document are for illustrative purposes only. Dialog Semiconductor makes no representation or warranty that such applications, software and semiconductor products will be suitable for the specified use without further testing or modification. Unless otherwise agreed in writing, such testing or modification is the sole responsibility of the customer and Dialog Semiconductor excludes all liability in this respect.

Customer notes that nothing in this document may be construed as a license for customer to use the Dialog Semiconductor products, software and applications referred to in this document. Such license must be separately sought by customer with Dialog Semiconductor.

All use of Dialog Semiconductor products, software and applications referred to in this document are subject to Dialog Semiconductor's Standard Terms and Conditions of Sale, available on the company website (www.dialog-semiconductor.com) unless otherwise stated.

Dialog and the Dialog logo are trademarks of Dialog Semiconductor plc or its subsidiaries. All other product or service names are the property of their respective owners.

© 2018 Dialog Semiconductor. All rights reserved.

RoHS Compliance

Dialog Semiconductor's suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

Contacting Dialog Semiconductor

United Kingdom (Headquarters) Dialog Semiconductor (UK) LTD Phone: +44 1793 757700

Germany

Dialog Semiconductor GmbH Phone: +49 7021 805-0

The Netherlands Dialog Semiconductor B.V. Phone: +31 73 640 8822 North America Dialog Semiconductor Inc. Phone: +1 408 845 8500

Japan Dialog Semiconductor K. K. Phone: +81 3 5769 5100

Taiwan Dialog Semiconductor Taiwan Phone: +886 281 786 222 Hong Kong Dialog Semiconductor Hong Kong Phone: +852 2607 4271

Korea Dialog Semiconductor Korea Phone: +82 2 3469 8200

China (Shenzhen) Dialog Semiconductor China Phone: +86 755 2981 3669

China (Shanghai) Dialog Semiconductor China Phone: +86 21 5424 9058

Product Summary

1.0