








[P.C.B.LAYOUT]



[Schematic]

NOTES:

1.Specification:

- 1>.Operation force:1000gf Max.
- 2>.Operation Temperature: -30°C to $+85^{\circ}\text{C}$.
- 3>.Storage Temperature: -40°C to $+85^{\circ}\text{C}$.
- 4>.Mechanical Life: 1000 cycles operations.
- 5>.Resistance to Soldering: $260\pm 5^{\circ}\text{C}$ for 3-5 Seconds.

2.PLATING:

- 1>.GOLD flash 1u"(min) SOLDERTAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>.Non-switch Rating:100mA at 50V DC.
- 2>.Switching Rating: 25mA at 24V DC.
- 3>.Contact Resistance: Initial 50m Ω Max.
Contact Resistance: After life 100m Ω Max.
- 4>.Insulation Resistance:100M Ω Min at 100VDC.
- 5>.Dielectric Strength: 300V AC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSHP XX I J G E R

- (包装方式:T=Tub R=Reel)
- (电镀层:E=接触位3u"/焊接位1-2u")
- (电镀层:G=端子内外电镀全金)
- (端脚型:S=贴片 / D=插件 / J型)
- (L=高柄 / S=低柄 / T=低柄贴胶)
- (开关位数: 02位-----10位)

5.PACKING: 2000pcs/Reel/Box.

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd				
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:PRODUCT Family DSHP Series Pitch 1.27mm			
			PAR	DSHP-04-TJ-GER		
			DWN			
			CHKD			
APVD						
DECIMALS:			ANGLES:			
>0±0.05	>0°±0.5°					
>1±0.10	>5°±1.0°					
>10±0.30						
			CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A