





Basic features

Approval/Conformity

CE
CSA
WEEE
1.5 ms

Bounce time max.

Switching time

Use with series

10 ms
EGT F60
RGT 100
RGT 61
RGT 62
RGT 72

Mechanical Cam Switches
BSE 30.0-RK
Order Code: BSE0005

BALLUFF

Electrical connection

Connection	M3
Connection type	1. Switch position: Screw terminal
Contact system	Dual changeover One NO and one NC galvanically isolated Double-interrupting

Electrical data

Contact arrangement	NC: 21+22 NO: 13+14
Contact resistance max.	40 mOhm
Contact resistance max., note	New condition
Continuous current	1. Switch position: 6.0 A
Mechanical life expectancy min.	30 mil. switching operations
Minimum load at 24 V DC	20.0 mA
Nominal voltage	250 VAC
Switching actuation force max.	4.80 N
Switching capacity at 220 V DC	0.5 A, L/R = 200ms
Switching capacity at 24 V DC	4 A, L/R = 200 ms
Switching capacity at 250 V AC	1 A cos φ = 0.4 2 A cos φ = 0.8 6 A cos φ = 1
40...60Hz	
Switching operations per minute	300
Switching principle	Snap switch, self-cleaning
Switchover time max.	10.0 ms

Environmental conditions

Ambient temperature	-5...85 °C
---------------------	------------

Material

Cover material	Thermoplast
Housing material	Thermoplast, GF
Material contacts	Silver, gold plated
Material contacts	1. Switch position: Silver, gold plated

Mechanical data

Connection cross-section	1.5 mm ²
Switching actuation force min.	3.60 N
Tightening torque max.	120 Ncm