


COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICATION STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C			STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C			
	VOLTAGE	AC 50 V			OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY : 95 % MAX (NO DEW CONDENSATION IS PERMITTED)			
	CURRENT	0.3 A							
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENT			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING			X	X
MARKING		CONFIRMED VISUALLY.						X	X
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			70 mΩ MAX.			X	X
INSULATION RESISTANCE		100 V DC.			100 MΩ MIN.			X	—
VOLTAGE PROOF		150 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN			X	X
MECHANICAL CHARACTERISTICS									
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE: 60 N MAX. WITHDRAWAL FORCE: 2.5 N MIN.			X	—
MECHANICAL OPERATION		50 TIMES INSERTION AND EXTRACTIONS.			1)CONTACT RESISTANCE: 80 mΩ MAX 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	—
VIBRATION		FREQUENCY: 10 TO 55 Hz. SINGLE AMPLITUDE: 0.75 mm. — m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.			1)NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2)NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.						X	—
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h.			1)CONTACT RESISTANCE: 80 mΩ MAX. 2)INSULATION RESISTANCE: 100 MΩ MIN.			X	—
RAPID CHAGE OF TEMPERTURE		TEMPERTURE -55→15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→2~ 3min. UNDER 5 CYCLES.			3)NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	—
DRY HEAT		EXPOSED AT 85 °C, 96 h.			1)CONTACT RESISTANCE: 80 mΩ MAX.			X	—
COLD		EXPOSED AT -55 °C, 96 h.			2)NO DAMAGE, CRACK AND LOOSENESS OF PART.				
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.			X	—
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JIS C 0090)			1)CONTACT RESISTANCE: 80 mΩ MAX 2)NO HEAVY CORROSION.			X	—
RESISTANCE TO SOLDERING HEAT		REFLOW RECOMMENDED TEMPERATURE PROFILE  25°C (160 S) 150°C 160°C (30 S) 240°C (5 S MAX) 200°C 60~90 S 20~30 S TO BE TESTED UNDER THE ABOVE CONDITIONS.			NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.			X	—
SOLDRABILITY		SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR IMMERSION DURATION, 2 s.			NO PINHOLE OR DEWETTING ON SOLDERED SURFACE.			X	—
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				<i>J. Matsukawa</i>	<i>J. Matsukawa</i>	<i>M. Sakuchi</i>	<i>T. Yoshimura</i>		
UNLESS OTERWISE SPECIFIED ,REFER TO JIS C 5402.				00.01.15	00.01.15	00.01.17	00.01.17		
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST									
HS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. FX11B - 100S - SV		
CODE NO.(OLD)		DRAWING NO.		CODE NO		1/1			
CL		ELC4 - 152645 -		CL 573 - 0753 - 0 -		1			