PulseLARSEN Antennas

TECHNICAL DATA SHEET

Series: Ceramic Chip

Description:
2.5-2.69GHz Ceramic SMT Antenna

PART NUMBER: W3020



Features:

- Omnidirectional radiation
- Low profile
- Compact size:
  W x L x H (3.2 x1.6 x 1.1mm)
- Fully SMD compatible
- Lead free soldering compatible
- Tape and reel packing
- RoHS compliant
- Moisture Sensitivity Level MSL3

Applications:

- 2.5-2.69 GHz Radios
- LTE B38, B41
- Devices needing smallest form factor high performing miniature antenna

All dimensions are in mm / inches

Issue: 1821

RoHS COMPLIANT

For more information:

Pulse Worldwide Headquarters
15255 Innovation Drive #100
San Diego, CA 92128
USA
Tel:1-858-674-8100

Pulse/Larsen Antennas
18110 SE 34th St Bldg 2 Suite 250
Vancouver, WA 98683
USA
Tel: 1-360-944-7551

Europe Headquarters
Pulse GmbH & Do, KG
Zeppelinstrasse 15
Herrenberg, Germany
Tel: 49 7032 7806 0

Pulse (Suzhou) Wireless Products Co, Inc.
99 Huo Ju Road(#29 Bldg,4th Phase
Suzhou New District
Jiangsu Province, Suzhou 215009 PR China
Tel: 86 512 6807 9998

Series: Ceramic Chip

Description:
2.5-2.69GHz Ceramic SMT Antenna

PART NUMBER: W3020

ELECTRICAL SPECIFICATIONS

Frequency	2.5-2.69 GHz
Nominal Impedance	50 Ω
Return Loss(Typical)*	<-5.5dB
Max Gain*	2.9dBi (Peak)
	1.5dBi (Band Edges)
Radiation Efficiency*	89%/-0.52dB (Peak)
	72%/-1.43dB(Band Edges)

Note: Electrical characteristics depend on test board (GP) size and antenna positioning on GP and Ground Clearance area size.

**Tested on PULSE test board position 1 (refer to page 10) . The testboard size 80x35 mm, PCB ground clearance area 4.0 x 6.25 mm. 1.0pF shunt matcing capacitor used.*

RoHS COMPLIANT

Series: Ceramic Chip

Description:
2.5-2.69GHz Ceramic SMT Antenna

PART NUMBER: W3020

MECHANICAL SPECIFICATIONS

Weight	0.033 g
Size	3.2 x1.6 x 1.1mm

ENVIRONMENTAL SPECIFICATIONS

Operating temperature	-40~+85° C
Temperature	-40~+85° C
Humidity	Cyclic 6 +25° C/+55° C 95%
Vibration	
Sinusoidal 2-8Hz	7.5 mm
Sinusoidal 8-200Hz	20 m/s²
Shocks	0.5 m/s
Salt mist	96 hours

RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

MECHANICAL DRAWING AND TERMINAL CONFIGURATION



1. Antenna is symmetrical, both of antenna pattern have same RF performance.
2. The size of slot is only for reference.

RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

MECHANICAL DRAWING AND TERMINAL CONFIGURATION





No.	Terminal Name	Terminal Dimensions
1	Feed / GND	0.62 x 1.36 mm
2	Feed / GND	0.62 x 1.36 mm
Antenna is symmetrical. Either of terminals 1 or 2 can be Feed / GND		

RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

PCB Layout

Ground cleared under antenna, clearance area 4.00 x 6.25 mm

Matching and tuning component value and placement depend on application and surrounding mechanics / materials.

Feed line should be designed to match 50 Ω characteristic impedance, depending on PWB material and thickness.

Recommended test board layout for electrical characteristic measurement, test board outline size 80 x 37 mm.





Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

PCB Layout

Ground clearance area (4,00 x 6,25 mm)



DETAIL A

Opening in bottom/inner ground layers



DETAIL B

Opening in other layers (no ground/ RF)



DETAIL C

Issue: 1821

RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

PCB Layout

Pad dimensions in top copper



DETAIL D

Antenna position on PWB layout



DETAIL E

RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

PCB Layout



DETAIL F



DETAIL G



DETAIL H

RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

PCB Layout

Pulse test PWB size is 37 x 80 mm, other sized boards can be used depending on customer device size (minimum 35 x 35 mm)





Series: Ceramic Chip

Description:
2.5-2.69GHz Ceramic SMT Antenna

PART NUMBER: W3020

CHARTS

Ground cleared under antenna, clearance area 4.00 x 6.25 mm

Typical Electrical Characteristics (T=25 ℃)

Measured on the 80 x 37mm test board with matching circuit (shunt 1.0 pF) and in antenna position 1 on PWB layout, see page 9.





Typical Return Loss S11/ impedance, free space efficiency and gain





RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

CHARTS

Typical Free Space Radiation Patterns

XZ-PLANE



ZY-PLANE



XY-PLANE





RoHS COMPLIANT

Description:
2.5-2.69GHz Ceramic SMT Antenna

Series: Ceramic Chip

PART NUMBER: W3020

PACKAGING

3000pcs antennas per 7” reel

5pcs 7” reel per inner package box

2pcs inner box per out box

Total 30000pcs antenna per out box

Out box size: 390mmx215mmx165mm





According to MSL3 packing requirement, MBB-Moisture Barrel Bag, Desiccant, HIC-Humidity Indicator Card, MSID Label, Caution Label are required.