

SMA Male Right Angle to TNC Male Cable Assembly using LC141TB Coax, 10 FT

#### LCCA30426-FT10

## Configuration

· Connector 1: SMA Male Right Angle

Connector 2: TNC MaleCable Type: LC141TB

#### **Features**

- · Max Frequency 6 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.9% VoP

#### **Applications**

- General Purpose
- · Laboratory Use

- Hand Formable
- Tin Filled Copper Braid Outer Conductor
- · System Interconnect



#### Description

L-com's LCCA30426-FT10 is a SMA male right angle to TNC male cable assembly using LC141TB coax, 10 FT and ships same-day. The LC141TB coax of this SMA cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com SMA to TNC cable assembly has a male to male gender configuration with formable LC141TB series coax and operates to 6 GHz. The tinned copper braid outer conductor is easily formed by hand with an overall diameter of inches and excellent shielding effectiveness greater than 110dB. This right angle SMA cable interface on the LC141TB coax allows for easier connections in tight spaces.

Custom versions of this SMA male to SMA male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30426-FT10 L-com SMA Male Right Angle to TNC Male Cable Assembly using LC141TB Coax, 10 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.



# SMA Male Right Angle to TNC Male Cable Assembly using LC141TB Coax, 10 FT



#### LCCA30426-FT10

## **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.45:1	
Velocity of Propagation		69.5		%
RF Shielding	110			dB
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Con	ductor	7.8 [25.59]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Cor	nductor	5.5 [18.04]		Ohms/1000ft [Ohms/Km]

## **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	6		GHz
Insertion Loss (Max.)	1	1.4	2.03	3.4		dB

#### **Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

## **Mechanical Specifications**

#### **Cable Assembly**

120 in [304.8 cm] Length Diameter 0.591 in [15.01 mm]

#### Cable

LC141TB Cable Type Impedance 50 Ohms Inner Conductor Type Solid

Copper, Silver Inner Conductor Material and Plating

Dielectric Type **PTFE** 

Outer Conductor Material and Plating **Tinned Copper Braid** 

Repeated Minimum Bend Radius 0.625 in [15.88 mm]



SMA Male Right Angle to TNC Male Cable Assembly using LC141TB Coax, 10 FT



## LCCA30426-FT10

#### **Connectors**

Description	Connector 1	Connector 2	
Туре	SMA Male Right Angle	TNC Male	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold over Nickel	Brass, Gold over Nickel	
Dielectric Type	PTFE	PTFE	
Body Material and Plating	Brass, Gold over Nickel	Brass, Nickel	
Coupling Nut Material and Plating	Passivated Stainless Steel	Brass, Nickel	
Hex Size	5/16 inch		
Torque	8 in-lbs 0.9 Nm		

## **Environmental Specifications**

**Temperature** 

Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

## **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.



SMA Male Right Angle to TNC Male Cable Assembly using LC141TB Coax, 10 FT



#### LCCA30426-FT10

#### **How to Order**

active components.



Example: LCCA30426-12 = 12 inches long cable LCCA30426-100cm = 100 cm long cable

SMA Male Right Angle to TNC Male Cable Assembly using LC141TB Coax, 10 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

## **L-com CAD Drawing**

