



### LCCA30507-FT6

### Configuration

Connector 1: BNC FemaleConnector 2: N FemaleCable Type: LC141TBJ

#### **Features**

- · Max Frequency 2 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 70.0% VoP

### **Applications**

- General Purpose
- · Laboratory Use

- Hand Formable
- Tin Filled Copper Braid Outer Conductor
- FEP Jacket
- · System Interconnect



### **Description**

L-com's LCCA30507-FT6 is a BNC female to N female cable assembly using LC141TBJ coax, 6 FT and ships same-day. The LC141TBJ coax of this BNC cable uses the PTFE dielectric with a VoP of 70%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com BNC to N cable assembly has a female to female gender configuration with formable LC141TBJ series coax and operates to 2 GHz. The jacketed tinned copper braid outer conductor is easily formed by hand with an overall diameter of 0.161 inches and excellent shielding effectiveness greater than 100dB.

Custom versions of this BNC female to BNC female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30507-FT6 L-com BNC Female to N Female Cable Assembly using LC141TBJ Coax, 6 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





### LCCA30507-FT6

## **Electrical Specifications**

Minimum	Typical	Maximum	Units
DC		2	GHz
		1.45:1	
	70		%
100			dB
	1.43 [4.69]		ns/ft [ns/m]
	29 [95.14]		pF/ft [pF/m]
tor	7.28 [23.88]		Ohms/1000ft [Ohms/Km]
tor	5.5 [18.04]		Ohms/1000ft [Ohms/Km]
	DC 100	TO  70  100  1.43 [4.69]  29 [95.14]  or  7.28 [23.88]	DC 2 1.45:1 70 100 1.43 [4.69] 29 [95.14] or 7.28 [23.88]

# **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2			GHz
Insertion Loss (Typ.)	0.7	0.95	1.22			dB

### **Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

## **Mechanical Specifications**

### **Cable Assembly**

Length 72 in [182.88 cm]

Cable

Cable Type LC141TBJ
Impedance 50 Ohms
Inner Conductor Type Solid

Inner Conductor Material and Plating Copper, Silver

Dielectric Type PTFE

Outer Conductor Material and Plating Tinned Copper Braid Jacket Material FEP, Black

Jacket Diameter 0.161 in [4.09 mm]

One Time Minimum Bend Radius 0.315 in [8 mm]
Repeated Minimum Bend Radius 1.575 in [40.01 mm]





# LCCA30507-FT6

### **Connectors**

Connector 1	Connector 2
BNC Female	N Female
50 Ohms	50 Ohms
	Phosphor Bronze, Gold over Nickel
	PTFE
Brass, Nickel	Brass, Nickel
	BNC Female 50 Ohms

**Environmental Specifications** 

**Temperature** 

Operating Range -65 to +150 deg C

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 


Notes:





### LCCA30507-FT6

### **How to Order**



Example: LCCA30507-12 = 12 inches long cable

LCCA30507-100cm = 100 cm long cable

BNC Female to N Female Cable Assembly using LC141TBJ Coax, 6 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

### **L-com CAD Drawing**

