

#### LCCA30538-FT3



#### Configuration

- · Connector 1: BNC Female
- · Connector 2: SMA Female Bulkhead
- Cable Type: LC085TB


#### **Features**

- · Max Frequency 1 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.5% VoP

#### **Applications**

- General Purpose
- · Laboratory Use

- Hand Formable
- Tin Filled Copper Composite Braid Outer Conductor
- · System Interconnect



#### Description

L-com's LCCA30538-FT3 is a BNC female to SMA female bulkhead cable assembly using LC085TB coax, 3 FT and ships same-day. The LC085TB coax of this BNC cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com BNC to SMA cable assembly has a female to female gender configuration with formable LC085TB series coax and operates to 1 GHz. The tin plated copper outer conductor can be easily formed by hand and has an overall diameter of 0.085 inches. L-com's RF cable assembly with SMA bulkhead interface enables system designers to have external connections on their product enclosures or to be used for other rack mount and panel mount applications.

Custom versions of this BNC female to BNC female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30538-FT3 L-com BNC Female to SMA Female Bulkhead Cable Assembly using LC085TB Coax, 3 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.





#### LCCA30538-FT3

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.45:1	
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conduc	tor	65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conduc	ctor	10.2 [33.46]		Ohms/1000ft [Ohms/Km]

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	500	1,000				MHz
Insertion Loss (Typ.)	0.65	0.89				dB

#### **Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

#### **Mechanical Specifications**

#### **Cable Assembly**

Length 36 in [914.4 mm]

#### Cable

Cable Type LC085TB
Impedance 50 Ohms
Inner Conductor Type Solid

Inner Conductor Material and Plating Copper Clad Steel, Silver

Dielectric Type PTFE
Number of Shields 1

Outer Conductor Material and Plating Copper, Tin
Outer Conductor Diameter 0.085 in [2.16 mm]

Repeated Minimum Bend Radius 0.78 in [19.81 mm]



# i de la companya de l

#### LCCA30538-FT3

#### **Connectors**

Description	Connector 1	Connector 2
Туре	BNC Female	SMA Female Bulkhead
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold over Nickel
Contact Plating Specification	30 μin minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Gold over Nickel
Body Plating Specification	100 μin minimum	
Seal Gasket Material	Silicone	

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 

Notes:



## First Control of the Control of the

#### LCCA30538-FT3

#### **How to Order**

active components.



Example: LCCA30538-12 = 12 inches long cable LCCA30538-100cm = 100 cm long cable

BNC Female to SMA Female Bulkhead Cable Assembly using LC085TB Coax, 3 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

#### **L-com CAD Drawing**

