

N Male Right Angle to TNC Female Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30582-FT6

### Configuration

- Connector 1: N Male Right Angle
- Connector 2: TNC Female
- Cable Type: LC085TB

### Features

- Max Frequency 6 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.5% VoP
- Hand Formable
- Tin Filled Copper Composite Braid Outer Conductor

### Applications

- General Purpose
- Laboratory Use
- System Interconnect



### Description

L-com's LCCA30582-FT6 is a N male right angle to TNC female cable assembly using LC085TB coax, 6 FT and ships same-day. The LC085TB coax of this N cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com N to TNC cable assembly has a male to female gender configuration with formable LC085TB series coax and operates to 6 GHz. The tin plated copper outer conductor can be easily formed by hand and has an overall diameter of 0.085 inches. This right angle N cable interface on the LC085TB coax allows for easier connections in tight spaces.

Custom versions of this N male to N female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30582-FT6 L-com N Male Right Angle to TNC Female Cable Assembly using LC085TB Coax, 6 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

N Male Right Angle to TNC Female Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30582-FT6

### Electrical Specifications

| Description                   | Minimum | Typical       | Maximum | Units                 |
|-------------------------------|---------|---------------|---------|-----------------------|
| Frequency Range               | DC      |               | 6       | GHz                   |
| VSWR                          |         |               | 1.45:1  |                       |
| Velocity of Propagation       |         | 69.5          |         | %                     |
| Capacitance                   |         | 29 [95.14]    |         | pF/ft [pF/m]          |
| DC Resistance Inner Conductor |         | 65.7 [215.55] |         | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor |         | 10.2 [33.46]  |         | Ohms/1000ft [Ohms/Km] |

### Specifications by Frequency

| Description           | F1  | F2   | F3  | F4  | F5 | Units |
|-----------------------|-----|------|-----|-----|----|-------|
| Frequency             | 0.5 | 1    | 2.5 | 6   |    | GHz   |
| Insertion Loss (Typ.) | 1.2 | 1.68 | 2.4 | 3.9 |    | dB    |

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

### Mechanical Specifications

#### Cable Assembly

|          |                    |
|----------|--------------------|
| Length   | 72 in [182.88 cm]  |
| Diameter | 0.79 in [20.07 mm] |

#### Cable

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Type                           | LC085TB                   |
| Impedance                            | 50 Ohms                   |
| Inner Conductor Type                 | Solid                     |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |
| Number of Shields                    | 1                         |
| Outer Conductor Material and Plating | Copper, Tin               |
| Outer Conductor Diameter             | 0.085 in [2.16 mm]        |
| Repeated Minimum Bend Radius         | 0.78 in [19.81 mm]        |

N Male Right Angle to TNC Female Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30582-FT6

### Connectors

| Description                       | Connector 1        | Connector 2                        |
|-----------------------------------|--------------------|------------------------------------|
| Type                              | N Male Right Angle | TNC Female                         |
| Impedance                         | 50 Ohms            | 50 Ohms                            |
| Contact Material and Plating      | Brass, Gold        | Beryllium Copper, Gold over Nickel |
| Dielectric Type                   | PTFE               | PTFE                               |
| Body Material and Plating         | Brass, Nickel      | Brass, Nickel                      |
| Coupling Nut Material and Plating | Brass, Nickel      |                                    |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

N Male Right Angle to TNC Female Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30582-FT6

### How to Order

Part Number Configuration:

**LCCA30582**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: LCCA30582-12 = 12 inches long cable  
LCCA30582-100cm = 100 cm long cable

N Male Right Angle to TNC Female Cable Assembly using LC085TB Coax, 6 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

## L-com CAD Drawing

