

## BNC Female Bulkhead to SMA Male Right Angle Cable Assembly using LC085TB Coax, 6 FT

### LCCA30535-FT6



#### Configuration

- Connector 1: BNC Female Bulkhead
- Connector 2: SMA Male Right Angle
- Cable Type: LC085TB

#### Features

- Max Frequency 1 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.5% VoP
- Hand Formable
- Tin Filled Copper Composite Braid Outer Conductor

#### Applications

- General Purpose
- Laboratory Use
- System Interconnect



#### Description

L-com's LCCA30535-FT6 is a BNC female bulkhead to SMA male right angle cable assembly using LC085TB coax, 6 FT and ships same-day. The LC085TB coax of this BNC cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com BNC to SMA cable assembly has a female to male gender configuration with formable LC085TB series coax and operates to 1 GHz. The tin plated copper outer conductor can be easily formed by hand and has an overall diameter of 0.085 inches. L-com's RF cable assembly with BNC bulkhead interface enables system designers to have external connections on their product enclosures or to be used for other rack mount and panel mount applications. This right angle SMA cable interface on the LC085TB coax allows for easier connections in tight spaces.

Custom versions of this BNC female to BNC male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30535-FT6 L-com BNC Female Bulkhead to SMA Male Right Angle Cable Assembly using LC085TB Coax, 6 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

BNC Female Bulkhead to SMA Male Right Angle Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30535-FT6

### Electrical Specifications

| Description                   | Minimum | Typical       | Maximum | Units                 |
|-------------------------------|---------|---------------|---------|-----------------------|
| Frequency Range               | DC      |               | 1,000   | MHz                   |
| VSWR                          |         |               | 1.45:1  |                       |
| Velocity of Propagation       |         | 69.5          |         | %                     |
| Capacitance                   |         | 29 [95.14]    |         | pF/ft [pF/m]          |
| DC Resistance Inner Conductor |         | 65.7 [215.55] |         | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor |         | 10.2 [33.46]  |         | Ohms/1000ft [Ohms/Km] |

### Specifications by Frequency

| Description           | F1  | F2    | F3 | F4 | F5 | Units |
|-----------------------|-----|-------|----|----|----|-------|
| Frequency             | 500 | 1,000 |    |    |    | MHz   |
| Insertion Loss (Typ.) | 1.2 | 1.68  |    |    |    | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly.  
The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

### Mechanical Specifications

#### Cable Assembly

Length 72 in [182.88 cm]

#### Cable

Cable Type LC085TB  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Steel, Silver  
Dielectric Type PTFE  
Number of Shields 1  
Outer Conductor Material and Plating Copper, Tin  
Outer Conductor Diameter 0.085 in [2.16 mm]  
  
Repeated Minimum Bend Radius 0.78 in [19.81 mm]

BNC Female Bulkhead to SMA Male Right Angle Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30535-FT6

### Connectors

| Description                       | Connector 1         | Connector 2                |
|-----------------------------------|---------------------|----------------------------|
| Type                              | BNC Female Bulkhead | SMA Male Right Angle       |
| Impedance                         | 50 Ohms             | 50 Ohms                    |
| Contact Material and Plating      | Brass, Gold         | Brass, Gold over Nickel    |
| Contact Plating Specification     | 30 µin minimum      | 8 µin minimum              |
| Dielectric Type                   | PTFE                | PTFE                       |
| Body Material and Plating         | Brass, Nickel       | Brass, Gold over Nickel    |
| Body Plating Specification        | 100 µin minimum     | 4 µin minimum              |
| Coupling Nut Material and Plating |                     | Passivated Stainless Steel |
| Hex Size                          |                     | 5/16 inch                  |
| Torque                            |                     | 8 in-lbs 0.9 Nm            |
| Seal Gasket Material              | Silicone            |                            |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

BNC Female Bulkhead to SMA Male Right Angle Cable  
Assembly using LC085TB Coax, 6 FT



## LCCA30535-FT6

### How to Order

Part Number Configuration:

**LCCA30535**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: LCCA30535-12 = 12 inches long cable  
LCCA30535-100cm = 100 cm long cable

BNC Female Bulkhead to SMA Male Right Angle Cable Assembly using LC085TB Coax, 6 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

## L-com CAD Drawing

