

N Female to TNC Male Right Angle Cable Assembly using LC141TBJ Coax, 5 FT

LCCA30519-FT5



Configuration

· Connector 1: N Female

Connector 2: TNC Male Right Angle

• Cable Type: LC141TBJ

Features

· Max Frequency 6 GHz


Shielding Effectivity > 100dB

• PTFE Dielectric with 70.0% VoP

Applications

- · General Purpose
- · Laboratory Use

- Hand Formable
- Tin Filled Copper Braid Outer Conductor
- FEP Jacket
- · System Interconnect



Description

L-com's LCCA30519-FT5 is a N female to TNC male right angle cable assembly using LC141TBJ coax, 5 FT and ships same-day. The LC141TBJ coax of this N cable uses the PTFE dielectric with a VoP of 70%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com N to TNC cable assembly has a female to male gender configuration with formable LC141TBJ series coax and operates to 6 GHz. The jacketed tinned copper braid outer conductor is easily formed by hand with an overall diameter of 0.161 inches and excellent shielding effectiveness greater than 100dB. This right angle TNC cable interface on the LC141TBJ coax allows for easier connections in tight spaces.

Custom versions of this N female to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30519-FT5 L-com N Female to TNC Male Right Angle Cable Assembly using LC141TBJ Coax, 5 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.



N Female to TNC Male Right Angle Cable Assembly using LC141TBJ Coax, 5 FT

LCCA30519-FT5

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.45:1	
Velocity of Propagation		70		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Con	ductor	7.28 [23.88]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Cor	nductor	5.5 [18.04]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	6		GHz
Insertion Loss (Typ.)	0.61	0.83	1.15	1.95		dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

Mechanical Specifications

Cable Assembly

60 in [152.4 cm] Length Diameter 0.63 in [16 mm]

Cable

Cable Type LC141TBJ 50 Ohms Impedance Inner Conductor Type Solid Inner Conductor Material and Plating Copper, Silver

Dielectric Type **PTFE**

Outer Conductor Material and Plating **Tinned Copper Braid** Jacket Material

FEP, Black Jacket Diameter 0.161 in [4.09 mm]

One Time Minimum Bend Radius 0.315 in [8 mm] Repeated Minimum Bend Radius 1.575 in [40.01 mm]



N Female to TNC Male Right Angle Cable Assembly using LC141TBJ Coax, 5 FT

O THE STATE OF THE

LCCA30519-FT5

Connectors

Description	Connector 1	Connector 2	
Туре	N Female	TNC Male Right Angle	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Phosphor Bronze, Gold over Nickel	Brass, Gold over Nickel	
Dielectric Type	PTFE	PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Coupling Nut Material and Plating		Brass, Nickel	

Environmental Specifications

Temperature

Operating Range -65 to +150 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:




N Female to TNC Male Right Angle Cable Assembly using LC141TBJ Coax, 5 FT

OHD TO THE REAL PROPERTY OF THE PARTY OF THE

LCCA30519-FT5

How to Order



Example: LCCA30519-12 = 12 inches long cable

LCCA30519-100cm = 100 cm long cable

N Female to TNC Male Right Angle Cable Assembly using LC141TBJ Coax, 5 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

