






RoHS
Compatible



NOTES:

- MATERIAL: GROUND CONTACT: C5210
CONTACT: C2680
HOUSING: LCP, UL94V-0, WHITE
- PLATING SPECIFICATION :
NICKEL PLATED FIRST, NICKEL PLATED WITH GOLD PLATING SPECIFICATION :
GROUND CONTACT NICKEL PLATING 1.0μmMIN, GOLD PLATED 0.025μmMIN;
CONTACT NICKEL PLATING 1.0μmMIN, GOLD PLATED 0.025μmMIN;
NO PLATING RESIDUE SALT SPRAY 48H
- FREQUENCY RANGE:
DC TO 9GHZ (VSWR: 1.3MAX AT 0.1~3GHZ, 1.4MAX AT 3~6GHZ 1.8MAX AT 6~9GHZ);
- CHARACTERISTIC IMPEDANCE: 50Ω(NOMINAL);
- TEMPERATURE: -40°C TO +90°C;
- RATED VOLTAGE: 60VAC;
- CONTACT RESISTANCE:
20mΩ MAX.(SIGNAL CONTACT)
10mΩ MAX.(GROUND CONTACT)
- WITHSTAND VOLTAGE: 200VAC FOR 1 MINUTE MIN;
- INSULATION RESISTANCE: 500MΩ MIN. AT 100VDC;
- MECHANICAL PERFORMANCE:
RECEPTACLE SHESRING STRENGTH: SHESRING STRENGTH 30N MIN
MATING FORCE ANG UNMATING FORCE:
MATING FORCE INITIAL: 30N MAX; AFTER 30CYCLES 30N MAX;
UNMATING FORCE INITIAL: 5N MIN; AFTER 30CYCLES 3N MIN ;
- COPLANAITY: 0.1MM MAX
- THIS COMPONENT IS HALOGEN FREE.



东莞市众驰电子科技有限公司

Dongguan Zhongchi Electronic Technology Co., Ltd Tel 0769-81238620 Fax: 0769-81238620

PART NAME: 1代板端


PART NO.: ZCIPX-2630125

DATE: 2023-09-12

APPROVED BY

CHECKED BY

DESIGNED BY



Tolerance

黄望春

UNITS: mm

SCALE: 1/1

REVISION: A

X.X ±0.50

X.XX ±0.15

X° ±3°