

SPECIFICATION FOR APPROVAL

規 格 書

Customer (客戶名稱): _____

Customer P/N(客戶番號): _____

Our P/N (本廠番號): FS87W16120-H32

Approval Date(日期): 2020.6.18

Environment Request(環境標準):

☐ Non-RoHS (非 RoHS 標準)

☒ RoHS (RoHS 標準)

☐ REACH (REACH 標準)

☐ Others (其他)

CUSTOMER'S APPROVED SIGNATURE

--	--	--



泰州福聲電子科技有限公司

Taizhou Fusheng Electronic Technology Co.,Ltd.

Adds: No168 of FengHuang Road West,Hailing District ,Taizhou .

地址：江蘇省泰州市海陵區鳳凰西路98號

Tel: +86-523-86219066

Fax: +86-523- 81601108

[Http://www.tzfsdz.com](http://www.tzfsdz.com)


E-mail: sales@electronic-tech.cn

	DESINGER	CHECKED	APPROVED
SIGNATURE			
DATE			

Speaker Specification

Part No.	Customer No 顧客型號			Customer code 顧客編號	
	Our Part No 本廠編號	FS87W16120-H32		Revision 版本	B
No.	Item 項目	Specification 規格	Testing Condition 測試條件		
1.	Rated Imp 共稱阻抗	16ohm±15%	At 1kHz13.86Vrms		
2.	Resonance Freq 最低共振周波數	370Hz±20%	Without Baffle		
3.	Output S.P.L. 出力音壓	96±3dB	At 1m 1w ,0.6,0.8,1.0,1.2KHz Average		
4.	Rated Power 定格入力	at 12.0W	at 13.86Vrms		
5.	Max Power 最大入力	at 15.0W	at 15.49 Vrms		
6.	Frequency Range 實效頻寬	FO----7kHz			
7.	Operation 可靠性試驗	Must Be Normal at Rated Frequency Range	Program Source 12W FO ----- 10kHz		
8.	Buzzes & Rattles 異常音試驗	Should not be audible buzz and rattle at Rated Frequency Range 無異常聲	Sine Wave Between (正弦波入力) at 13.86 Vrms / FO-- 10kHz		
9.	T H D 失真	≤5%			
10.	Magnet 磁鐵	Ferrite			
11.	Operating Temperature 動作溫度	-30℃ to +85℃			
12.	Storage Temperature 儲存溫度	-40℃ to +105℃			
13.	Weight 重量	240g±8%			

Product Outside View



产品图片Picture:




Frequency Response



Remark

NO	零件Component	材质Material
1	压边 Gasket	橡胶 Rubber
2	盆架 Frame	冷轧钢板SPCC
3	弹波 Damper	布 Cloth
4	华司Washer	冷轧钢板SPCC
5	磁铁 Magnet	铁氧体 Ferrite
6	T铁 T-yoke	冷轧钢板 SPCC
7	鼓纸 Cone	防水盆 PEI
8	音圈Voice Coil	胶管 KSV+Cu
9	帽子 Dust cap	防水帽 PEI
10	接线板 Terminals	纸+铁 Paper+Steel

包装Packing picture:



- 1. Each clapboard 24 pcs,
Each carton 2 clapboards,
48 pcs/carton
- 2. N.W: 11.5 KG,G.W:13.5 KG
- 3. Corrugated paper:365*325mm1pcs
- 4. Carton size:380*340*220 mm1 pcs

