




POLES	P/N	A	B
2	1.0T-2P-WT	1.00	4.50
3	1.0T-3P-WT	2.00	5.50
4	1.0T-4P-WT	3.00	6.50
5	1.0T-5P-WT	4.00	7.50
6	1.0T-6P-WT	5.00	8.50
7	1.0T-7P-WT	6.00	9.50
8	1.0T-8P-WT	7.00	10.50
9	1.0T-9P-WT	8.00	11.50
10	1.0T-10P-WT	9.00	12.50
11	1.0T-11P-WT	10.00	13.50
12	1.0T-12P-WT	11.00	14.50
13	1.0T-13P-WT	12.00	15.50
14	1.0T-14P-WT	13.00	16.50
15	1.0T-15P-WT	14.00	17.50
16	1.0T-16P-WT	15.00	18.50
17	1.0T-17P-WT	16.00	19.50
18	1.0T-18P-WT	17.00	20.50
19	1.0T-19P-WT	18.00	21.50
20	1.0T-20P-WT	19.00	22.50



- 技术参数 (SPECIFICATIONS)
- ◆ 额定电压: 50V AC DC
Voltage rating: 50V AC DC
 - ◆ 额定电流: 1.0A AC DC(28AWG)
Current rating: 1.0A AC DC(28AWG)
 - ◆ 耐压性: 500V AC/minute
Withstand voltage 500V AC/minute
 - ◆ 绝缘电阻: 100MΩ MIN.
Insulation resistance: 100MΩ MIN.
 - ◆ 接触电阻: 20mΩ MAX.(初始值)
Contact resistance: 20mΩ MAX.(Initial)
 - ◆ 工作温度: -25°C~+85°C
Working Temperature: -25°C~+85°C
 - ◆ 间距: 1.0 mm
Pitch: 1.0mm
- 材料 (MATERIAL)
- ◆ 绝缘体: 尼龙9T UL94V-0
Insulator: PA9T UL94V-0
 - ◆ 焊片: 磷青铜镀锡
Solder tab: Phosphor bronze TIN-Plating
 - ◆ 接触针: 磷青铜镀锡
Contact PIN: Phosphor bronze TIN-Plating

APPROVALS		DATE	HRO 韩荣® ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2022.10.9	TITLE:	Bar Connector Series	
CHECKED			PART NO.	1.0T-nP-WT	
APPROVALS			UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE		30~以上	±0.30	ANGLE	DRAWING NO.
		10~30	±0.20		
		5~10	±0.15	±2'	SHEET 1 OF 1
		~ 5	±0.10		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			