

SR380L

LOW VF SCHOTTKY RECTIFIERS



VOLTAGE:	80	Volts	CURRENT:	3	Amperes	DO-27(DO-201AD)	Marking and Polarity
FEATURES							
- Plastic package has Underwriters Laboratory Flammability Classification 94V-0 - Softest, fast switching capability - Low Forward Voltage Drop - High temperature soldering guaranteed:260 C/10 seconds at terminals - Lead Free Finish, RoHS Compliant							
MECHANICAL DATA							
Case: JEDEC DO-201AD molded plastic body Terminals: Plated axial leads, solderable per MIL-STD-750,method 2026 Mounting Position: Any Weight:App. 1.05 grams (0.0353 ounce)							
TYPICAL APPLICATIONS						Remark:	
Device optimized for low forward voltage drop to maximize efficiency in Power Supply applications						①. SR380L=Model No. ②. NH=niuhang trademark ③. FFDDK=Internal control code,According to actual changes ④. White band denotes cathode	

Maximum Ratings (Ratings at 25°C ambient temperature unless otherwise specified.)

Parameter	Symbol	SR380L	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	80	V
Maximum RMS voltage	V_{RMS}	56	V
Maximum DC blocking voltage	V_{DC}	80	V
Maximum average forward rectified current(see fig.1)	$I_{F(AV)}$	3	A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC method at rated TL)(see fig.5)	I_{FSM}	70	A

Electrical Characteristics (Ratings at 25°C ambient temperature unless otherwise specified.)

Parameter	Test Conditions		Symbol	SR380L			Unit
				Min.	Typ.	Max.	
Maximum instantaneous forward voltage(see fig.2)(Note 1)	$T_A=25^{\circ}C$	$I_F=3A$	V_F	--	0.55	0.62	V
	$T_A=125^{\circ}C$			--	0.49	0.53	
Maximum instantaneous reversecurrent at rated DC blockingvoltage (see fig.3)(Note 1)	$T_A=25^{\circ}C$	$V_R=V_{RRM}$	I_R	--	50	100	μA
	$T_A=125^{\circ}C$	$V_R=80\%*V_{RRM}$		--	--	20	mA
Typical junction capacitance(see fig.4)	4V,1MHz		C_J	--	68	--	pF

Thermal Characteristcs (Ratings at 25°C ambient temperature unless otherwise specified)

Parameter	Symbol	SR380L	Unit
Operating junction	T_J	-65 to 150	$^{\circ}C$
Storage temperature range	T_{STG}	-65 to 150	
Typical thermal resistance (Note 2)	$R_{\theta JA}$	25	$^{\circ}C/W$
	$R_{\theta JL}$	8	

Note:

- Pulse width < 300 μs , Duty cycle < 2%
- Thermal resistance from junction to lead vertical P.C.B. mounted , 0.375"(9.5mm)lead length,Polymide PCB, 2 oz Copper.

SR380L

LOW VF SCHOTTKY RECTIFIERS



RATING AND CHARACTERISTIC CURVES




Fig.1- FORWARD CURRENT DERATING CURVE




Fig.2-TYPICAL INSTANTANEOUS FORWARD




Fig.3-TYPICAL REVERSE CHARACTERISTICS




Fig.4- TYPICAL JUNCTION CAPACITANCE




Fig.5-MAX. NON-REPETITIVE SURGE CURRENT




FIG.6-TYPICAL TRANSIENT THERMAL IMPEDANCE


SR380L

LOW VF SCHOTTKY RECTIFIERS



OUTLINE DRAWINGS

DO-27(DO-201AD)



OUTLINE DIMENSIONS

Dim.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	4.9	-	5.6	0.193	-	0.220
B	24.5	-	26.4	0.965	-	1.039
C	0.9	-	1.3	0.035	-	0.051
D	7.2	-	9.5	0.285	-	0.374

Packing Information

Package	Pack	Box Size L×W×H(mm)	Quantity (pcs/box)	Carton Size L×W×H(mm)	Quantity (pcs/carton)
DO-27(DO-201AD)	B/G	255*75*140	1250	410*280*330	12500

SR380L


LOW VF SCHOTTKY RECTIFIERS



Recommended wave soldering condition

Product	Peak Temperature	Soldering Time
Pb-free devices	260 +0/-5 °C	5 +1/-1 seconds

Recommended temperature profile for IR reflow



Profile feature	Sn-Pb eutectic Assembly	Pb-free Assembly
Average ramp-up rate (Tsmmax to Tp)	3°C/second max.	3°C/second max.
Preheat -Temperature Min(TS min) -Temperature Max(TS max) -Time(ts min to ts max)	100°C 150°C 60-120 seconds	150°C 200°C 60-180 seconds
Time maintained above: -Temperature (TL) - Time (tL)	183°C 60-150 seconds	217°C 60-150 seconds
Peak Temperature(TP)	240 +0/-5 °C	260 +0/-5 °C
Time within 5°C of actual peak temperature(tp)	10-30 seconds	20-40 seconds
Ramp down rate	6°C/second max.	6°C/second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

Note : All temperatures refer to topside of the package, measured on the package body surface.

SR380L

LOW VF SCHOTTKY RECTIFIERS



Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from niuhang Electronics co., LTD
- Niuhan Electronics co., LTD. reserves the rights to make changes of the content herein the document anytime without notification.
- Niuhan Electronics co., LTD. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Niuhan Electronics co., LTD. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Niuhan Electronics co., LTD. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Niuhan Electronics co., LTD. for any damages resulting from such improper use or sale.
- When the appearance of the product and chip size does not change, in order to product the customer quality, change the internal structure and the production process Niuhan can not notify