





注：本系列禁止转输、复制、编辑、修改、以及用其内容进行交流



REV	EC.N NO.	CONTENT	CHK	DATE
-----	----------	---------	-----	------

NOTES1:
UL Standard

Use group	B	C	D
Rated Current	15A	—	10A
Rated Voltage	300V	—	300V

3.Torque value: M2.5, 3.54Lb.in

4.Wire range: 28~12AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	4.0KV	/
Rate Voltage(V)	/	320V	/
Rate Current(A)	/	12A	/

2. Torque value: M2.5, 0.4Nm

3.wire range: 10~2.5mm²

NOTES2:

- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Cage: Brass (Ni Plated)
- 4.Clamp: Copper alloy (Ni Plated)
- 5.Screw: Steel (M2.5,Zn Plated)

NOTES3:

- 1.Pitch: 5.08mm Poles: 02-24P
- 2.Stripping length: 7-8mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MX2EDGKAM - 508 - XXP - XXXX - XX - X - X

产品型号 间距 颜色 极数 A-Z其他定制

灰色:GY 橙色:OE 01常规颜色 0:Y一字螺丝
蓝色:BU 红色:RD 02-99: 1:S十字螺丝
黑色:BK 透明色:TT 定制颜色 C:铜方块
绿色:GN 黄色:YW Fe:铁方块
透明色:TT 白色:WE

Pitch Range In		Nominal Dimension Range		In mm		mm	
Over	6	Over	10	Over	30	Over	60
TO	10	TO	24	TO	30	TO	60
6	10	24	30	60	100	150	150
±0.15		±0.20		±0.30		±0.50	
±0.20		±0.30		±0.50		±0.70	
±0.30		±0.50		±0.70		±1.00	
±0.50		±0.70		±1.00		±1.30	
±0.70		±1.00		±1.30		±2°	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	22.09.14	UNITS	MM
CHK	DATE	SCALE	1:1	A4	1/1
APP.	DATE	NAME	MX2EDGKAM-5.08-XXP		
CIXI MAIXU ELECTRONICS CO.,LTD					DWGNO.
MAIXU 慈溪市迈旭电子有限公司					