

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 8W
- temperature stable
- low cost

Applications

- harmonic rejection
- transmitters/receivers
- lab use

HT-VLF-190+




50Ω *DC to 190 MHz

electrical schematic



typical frequency response



Electrical Specifications at 25°C

PASSBAND (MHz) (loss < 1.2 dB) max.	fco, MHz Nom. (loss 3 dB) Typ.	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
		f 20 min.	40 typ.	fr 20 max.	Stopband Typ.	Passband Typ.	
DC~190	280	400	510-2850	6550	17	1.2	7

* Not for use with DC voltage at input and output ports

Typical Performance Data

(TEST CONDITIONS: INPUT POWER = 0dBm @ Temperature = +25°C)

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
40	0.26	1.08
100	0.44	1.08
170	0.71	1.10
190	0.83	1.12
250	1.65	1.47
280	3.15	2.13
310	6.83	3.46
340	13.47	4.47
375	25.46	3.89
400	37.43	3.86
510	40.97	12.99
850	57.21	52.65
1500	48.19	64.35
2850	37.12	64.35
6550	18.42	32.18
9000	28.00	6.03
12000	23.53	4.26

Maximum Ratings

Operating Temperature -55°C to 100°C


Storage Temperature -55°C to 100°C

RF Power Input* 8W at 25°C

DC Current Input to Output 0.5A max. at 25°C

* Passband rating, derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Outline Dimensions: Unit (mm)

B	10.41	E	7.92
D	36.32		
wt	10.0		

