

20V P-Channel Enhancement Mode MOSFET

General Features

- Proprietary Advanced Planar Technology ≻
- Rugged Polysilicon Gate Cell Structure ≻
- Fast Switching Speed ≻
- ≻ **RoHS** Compliant
- Halogen-free Available >

Applications

- High Efficiency SMPS ≻
- Adaptor/Charger ≻
- Active PFC ≻

BV _{DSS}	R _{DS(ON)} (Typ.)	ID			
-20V	5.2Ω	-280mA			



Ordering Information

Part Number	Package	Marking	Remark
FTZ50P01G5	SOT-23	P01	Halogen Free

Absolute Maximum Ratings

Absolute	Maximum Ratings	$T_A=25^{\circ}C$ unless otherwise spec			
Symbol	Parameter	FTZ50P01G5	Unit		
V _{DSS}	Drain-to-Source Voltage ^[1]	-20	V		
I _D	Continuous Drain Current	-0.28	٨		
I _{DM}	Pulsed Drain Current ^[2]	-1.12	— A		
P _D	Power Dissipation	0.5	W		
V _{GS}	Gate-to-Source Voltage	±20	V		
T_L	Soldering Temperature Distance of 1.6mm from case for 10 seconds	300	°C		
T_J and T_{STG}	Operating and Storage Temperature Range	-55 to 150			

Caution: Stresses greater than those listed in the "Absolute Maximum Ratings" may cause permanent damage to thedevice.

Thermal Characteristics

Symbol	Parameter	FTZ50P01G5	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	250	K/W

ARK Microelectronics Co., Ltd.

Electrical Characteristics

OFF Characteristics

OFF Characteristics					$T_A = 25$ °C unless otherwise specified	
Symbol	Parameter	Min.	Тур.	Max.	Unit	Test Conditions
BV _{DSS}	Drain-to-Source Breakdown Voltage	-20			V	$V_{GS}=0V, I_{D}=-250 \mu A$
I _{DSS}	Drain-to-Source Leakage Current		-0.23		nA	V_{DS} =-10V, V_{GS} =0V
I _{GSS}	Gate-to-Source Leakage Current		2		nA	V_{GS} =+20V, V_{DS} =0V
			-3			V_{GS} =-20V, V_{DS} =0V

ON Characteristics

 $T_A = 25 \degree C$ unless otherwise specified

Symbol	Parameter	Min.	Тур.	Max.	Unit	Test Conditions
R _{DS(ON)}	Static Drain-to-Source On-Resistance		5.2	-	Ω	V_{GS} =-10V, I_D =-50mA ^[3]
V _{GS(OFF)}	Gate-to-Source Cut-off Voltage		-4.38		V	$V_{GD}=0V, I_D=-1\mu A$
			-5.24		V	V _{GD} =0V, I _D =-250µA

Source-Drain Diode Characteristics				$T_A=25^{\circ}C$ unless otherwise specified		
Symbol	Parameter	Min	Тур.	Max.	Units	Test Conditions
V _{SD}	Diode Forward Voltage		1.13		V	I _{SD} =-50mA ^[3] , V _{GS} =0V

NOTE:

[1] T_J=+25°C to +150°C

[2] Repetitive rating, pulse width limited by maximum junction temperature. [3] Pulse width \leq 380µs; duty cycle \leq 2%.



Package Dimensions



SOT-23

ARK Microelectronics Co., Ltd.

www.ark-micro.com

Rev. 1.1 Jul. 2021



Published by ARK Microelectronics Co., Ltd. ADD: 4F,D26,UESTC National Science Park No. 1 Shuangxing Avenue, Gongxing Street, Shuangliu District, Chengdu, China (Sichuan) Pilot Free TradeZone. All Rights Reserved.

Disclaimers

ARK Microelectronics Co., Ltd. reserves the right to make change without notice in order to improve reliability, function or design and to discontinue any product or service without notice. Customers should obtain the latest relevant information before orders and should verify that such information is current and complete. All products are sold subject to ARK Microelectronics Co., Ltd.'s terms and conditions supplied at the time of order acknowledgement.

ARK Microelectronics Co., Ltd. warrants performance of its hardware products to the specifications at the time of sale, Testing, reliability and quality control are used to the extent ARK Microelectronics Co., Ltd deems necessary to support this warrantee. Except where agreed upon by contractual agreement, testing of all parameters of each product is not necessary performed.

ARK Microelectronics Co., Ltd. does not assume any liability arising from the use of any product or circuit designs described herein. Customers are responsible for their products and applications using ARK Microelectronics Co., Ltd.'s components. To minimize risk, customers must provide adequate design and operating safeguards.

ARK Microelectronics Co., Ltd. does not warrant or convey any license either expressed or implied under its patent rights, nor the rights of others. Reproduction of information in ARK Microelectronics Co., Ltd.'s data sheets or data books is permissible only if reproduction is without modification or alteration. Reproduction of this information with any alteration is an unfair and deceptive business practice. ARK Microelectronics Co., Ltd is not responsible or liable for such altered documentation.

Resale of ARK Microelectronics Co., Ltd.'s products with statements different from or beyond the parameters stated by ARK Microelectronics Co., Ltd. for the product or service voids all express or implied warrantees for the associated ARK Microelectronics Co., Ltd.'s product or service and are unfair and deceptive business practice. ARK Microelectronics Co., Ltd is not responsible or liable for any such statements.

Life Support Policy:

ARK Microelectronics Co., Ltd.'s products are not authorized for use as critical components in life devices or systems without the expressed written approval of ARK Microelectronics Co., Ltd.

As used herein:

- 1. Life support devices or systems are devices or systems which:
 - a. are intended for surgical implant into the human body,
 - b. support or sustain life,
 - c. whose failure to perform when properly used in accordance with instructions for used provided in the labeling, can be reasonably expected to result in significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.