


30V/18A N-Channel MOSFET

Features

- Advanced high cell density Trench technology
- Super Low Gate Charge
- Excellent CdV/dt effect decline
- Green Device Available

Application


- High Frequency Point-of-Load Synchronous Buck Converter for MB/NB/UMPC/VGA
- Networking DC-DC Power System
- Load Switch




Marking and pin assignment

Product Summary

V_{DS}	$R_{DS(ON)}$ MAX	I_D MAX
30V	5.5mΩ@10V	18A
	7.5mΩ@4.5V	



SOP-8 top view



Schematic diagram



Pb-Free



RoHS



Halogen-Free

Absolute Maximum Ratings (TA=25°C unless otherwise noted)







Symbol	Parameter	Rating	Unit
Common Ratings (TC=25°C Unless Otherwise Noted)			
V_{DS}	Drain-Source Breakdown Voltage	30	V
V_{GS}	Gate-Source Voltage	±20	V
T_J	Maximum Junction Temperature	150	°C
T_{STG}	Storage Temperature Range	-55 to 150	°C
I_S	Diode Continuous Forward Current	$T_c=25^\circ\text{C}$ 18	A

Mounted on Large Heat Sink




I_{DM}	Pulse Drain Current Tested	$T_c=25^\circ\text{C}$ 80	A
I_D	Continuous Drain Current@GS=10V	$T_c=25^\circ\text{C}$ 18	A
P_D	Maximum Power Dissipation	$T_c=25^\circ\text{C}$ 3	W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient>(*1 in2 Pad of 2-oz Copper), Max.)	40	°C/W

Electrical Characteristics (TJ=25°C unless otherwise noted)						
Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
BV _{(BR)DSS}	Drain-Source Breakdown Voltage	VGS=0V, ID=250μA	30	--	--	V
IDSS	Zero Gate Voltage Drain Current	VDS=30V, VGS=0V	--	--	1	uA
IGSS	Gate-Body Leakage Current	VGS=±20V, VDS=0V	--	--	±100	nA
VGS(th)	Gate Threshold Voltage	VDS=VGS, ID=250μA	1	1.5	2.5	V
RDS(on)	Drain-Source On-State Resistance	VGS=10V, ID=18A	--	4.7	5.5	mΩ
		VGS=4.5V, ID=15A	--	6.5	7.5	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
CISS	Input Capacitance	VDS=15V, VGS=0V, f=1MHz	--	2504	--	pF
COSS	Output Capacitance		--	323	--	pF
CRSS	Reverse Transfer Capacitance		--	283	--	pF
Switching Characteristics						
Qg	Total Gate Charge	VDS=15V, ID=18A, VGS=10V	--	54	--	nC
Qgs	Gate Source Charge		--	26	--	nC
Qgd	Gate Drain Charge		--	8.5	--	nC
td(on)	Turn-on Delay Time	VDD=20V, ID=2A, VGS=10V, RG=3Ω	--	11	--	nS
tr	Turn-on Rise Time		--	20	--	nS
td(off)	Turn-Off Delay Time		--	41	--	nS
tf	Turn-Off Fall Time		--	25	--	nS
Source- Drain Diode Characteristics						
VSD	Forward on voltage	Tj=25°C, Is=1A,	--	--	1.2	V

Typical Operating Characteristics



SOP-8 Package information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.450	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.007	0.010
D	4.700	5.100	0.185	0.201
e	1.270 (BSC)		0.050 (BSC)	
E	5.800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°