


**RECOMMEND P. C. B LAYOUT**  
PCB TOLERANCE: ±0.05 (TOP VIEW)

### SPECIFICATIONS

- Current Rating: 3Amps
- Insulation Resistance: 1000MΩ Min
- Contact Resistance: 20mΩ Max
- Withstanding Voltage: AC 1000V
- Operation Temperature: -40° to +105°
- Contact Material: Brass
- Standard: PA6T
- Insrlator Material: Polyester (UL 94V-0)
- Contact Plating: Gold Flash
- Max. Processing Temp: 240° C for 30-60 seconds  
(260° C for 5 seconds)



UNLESS OTHEWIXE SPECIFIED TOLERANCE										DRAWN NAME: 2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T	
X	:±0.30	X°	:±5°	SIZE	A4	SCALE	N:1	PROUCT NO.	ZX-PM2.54-2-6PY		
X.X	:±0.25	X.X°	:±1°	REV	A	UNIT	mm	PROJECT	☉	PAGE 1/1	
X.XX	:±0.20	X.XX°	:±0.5°	CHECKED:		CHECKED:	/ /	APPROVED:	/ /		

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60