


Description

The PESDNC2FD5VB protects sensitive semiconductor components from damage or upset due to electrostatic discharge (ESD) and other voltage induced transient events. They feature large cross-sectional area junctions for conducting high transient currents, offer desirable electrical characteristics for board level protection, such as fast response time, low operating voltage. It gives designer the flexibility to protect one bi-directional line in applications where arrays are not practical.



Feature

- 80W peak pulse power per line ($t_p = 8/20\mu s$)
- DFN1006 package
- Replacement for MLV(0402)
- Bidirectional configurations
- Response time is typically < 1ns
- Low clamping voltage
- RoHS compliant
- Transient protection for data lines to
IEC61000-4-2(ESD) ±30KV(air), ±30KV(contact);
IEC61000-4-4 (EFT) 40A (5/50ns)

Applications

- Cellular phones
- Portable devices
- Digital cameras
- Power supplies

Mechanical Characteristics

- Lead finish:100% matte Sn(Tin)
- Mounting position: Any
- Qualified max reflow temperature:260°C
- Device meets MSL 1 requirements
- Pure tin plating: 7 ~ 17 um
- Pin flatness: \leq 3mil

Absolute maximum rating@25°C

Rating	Symbol	Value	Units
Peak Pulse Power ($t_p=8/20\mu s$)	P_{pp}	80	W
Operating Temperature	T_J	-55 to +150	°C
Storage Temperature	T_{STG}	-55 to +150	°C




Fig 3.Typical Breakdown Voltage vs. Temperature




Fig 4.Typical Leakage Current vs. Temperature




Fig 5. Clamping voltage vs. Peak pulse current




Fig 6. Non-Repetitive Peak Pulse Power vs. Pulse time






Fig 7 TLP Measuremen

DFN1006 PACKAGE OUTLINE DIMENSIONS



Dim	Inches		Millimeters	
	MIN	MAX	MIN	MAX
A	0.013	0.020	0.34	0.50
B	0.000	0.002	0.00	0.05
C	0.037	0.042	0.95	1.075
D	0.021	0.026	0.55	0.675
E	0.017	0.021	0.45	0.55
F	0.007	0.011	0.20	0.30
H	0.015Typ.		0.40Typ.	
R	0.001	0.005	0.05	0.15

Marking



Ordering information

Order code	Package	Baseqty	Deliverymode
UMW PESDNC2FD5VB	DFN1006	10000	Tape and reel