


SOT-23 Plastic-Encapsulate Transistors

PNP Darlington Transistor

MARKING CODE: A63:2U

A64:2V

For general purpose application, darlington transistor



SOT-23

1. BASE 2. Emitter 3. Collector







Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Collector Base Voltage	$-V_{CBO}$	30	V
Collector Emitter Voltage	$-V_{CEO}$	30	V
Emitter Base Voltage	$-V_{EBO}$	10	V
Collector Current	$-I_C$	500	mA
Power Dissipation	P_{tot}	200	mW
Junction Temperature	T_j	150	$^\circ\text{C}$
Storage Temperature Range	T_s	- 55 to + 150	$^\circ\text{C}$

Characteristics at $T_a = 25^\circ\text{C}$

Parameter	Symbol	Min.	Max.	Unit
DC Current Gain at $-V_{CE} = 5 \text{ V}$, $-I_C = 10 \text{ mA}$	h_{FE} MMBTA63	5000	-	-
at $-V_{CE} = 5 \text{ V}$, $-I_C = 10 \text{ mA}$	h_{FE} MMBTA64	10000	-	-
at $-V_{CE} = 5 \text{ V}$, $-I_C = 100 \text{ mA}$	h_{FE} MMBTA63	10000	-	-
at $-V_{CE} = 5 \text{ V}$, $-I_C = 100 \text{ mA}$	h_{FE} MMBTA64	20000	-	-
Collector Cutoff Current at $-V_{CB} = 30 \text{ V}$	$-I_{CBO}$	-	100	nA
Emitter Cutoff Current at $-V_{EB} = 10 \text{ V}$	$-I_{EBO}$	-	100	nA
Collector Emitter Breakdown Voltage at $-I_C = 100 \mu\text{A}$	$-V_{(BR)CEO}$	30	-	V
Collector Emitter Saturation Voltage at $-I_C = 100 \text{ mA}$, $-I_B = 0.1 \text{ mA}$	$-V_{CE(sat)}$	-	1.5	V
Base Emitter On Voltage at $-V_{CE} = 5 \text{ V}$, $-I_C = 100 \text{ mA}$	$-V_{BE(on)}$	-	2	V
Transition Frequency at $-V_{CE} = 5 \text{ V}$, $I_E = 10 \text{ mA}$	f_T	125	-	MHz


Typical Characteristics



PACKAGE OUTLINE

Plastic surface mounted package; 3 leads

SOT-23



UNIT	A	B	bp	C	D	E	HE	A1	Lp
mm	1.40 0.95	2.04 1.78	0.50 0.35	0.19 0.08	3.10 2.70	1.65 1.20	3.00 2.20	0.100 0.013	0.50 0.20