

A				B				C				D				E				F				G			
性能参数																											
1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A																											
2. Rated current:2A/DC36V 额定电流:2A/DC36V																											
3. Power-frequency withstand voltage:1800V1min 工频耐压:1800V1min																											
4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ																											
5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ																											
6. Pressing stroke:2.20mm ± 0.10 按压行程:2.20mm ± 0.10																											
7. Contact stroke:1.00mm±0.10 接触行程 :1.00mm±0.10																											
8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N																											
9. Protection level:IP65 防护等级:IP65																											
10. Explosion prevention level: IK10 防暴等级: IK10																											
11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃																											
12. Compression torque: ≤ 4N 按压扭力: ≤4N																											
13. Electrical life: 200000 cycles 电气寿命: 200000 cycles																											
14. mechanical: 500000cycles 机械寿命: 500000cycles																											
15. Operation method:Self repeating form 操作方式: 自复式																											
16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N																											

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91901P2A																
A2							DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																
A1							ROCPCU TECHNOLOGY CO.,LTD																				
REV	DATE	REVISION	DESCRIPTION									ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission														
A				B				C				D				E				F				G			

	A	B	C	D	E	F	G
1	材质参数						1
2	7	Pin 引脚	Brass 黄铜	1	Silvering 镀银		2
	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银		
	5	Base 基座	PA66	1	Baby blue 浅蓝色		
3	4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍		3
	3	Oring O型圈	Silica gel 硅胶	1			
	2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色		
4	1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色		4
	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注		

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91901P2A
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					

A	B	C	D	E	F	G
---	---	---	---	---	---	---

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission