




A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91921G124RA5150
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X.X	± 0.15	ROC PU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				


A					B					C					D					E					F					G				
1	性能参数																																	
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A										13. Electrical life: 500000 cycles 电气寿命: 500000 cycles																							
	2. Rated current:3A/DC36V 额定电流:3A/DC36V										14. mechanical: 500000cycles 机械寿命: 500000cycles																							
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min										15. Operation method:Self-locking 操作方式: 自锁式																							
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ										16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N																							
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ										17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下																							
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10										18. LED lamp lifespan: 40000h LED寿命: 40000h																							
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10										19. LED color: Red LED颜色: 红色																							
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N																																	
	9. Protection level:IP67 防护等级:IP67																																	
2	10. Explosion prevention level: IK10 防暴等级: IK10																																	
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃																																	
	12. Compression torque: ≤ 4N 按压扭力: ≤4N																																	
3	连接形式																																	
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下																																	
	2. Can be used with dedicated connectors: 可配专用接插件使用:																																	
	2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)																																	
	2.2 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极																																	
4																																		
5																																		

A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91921G124RA5150
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					ROC PU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION								
					COMMON	TOLERANCE	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				

A					B					C					D					E					F					G				
---	--	--	--	--	---	--	--	--	--	---	--	--	--	--	---	--	--	--	--	---	--	--	--	--	---	--	--	--	--	---	--	--	--	--

A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑料		1							
9	LEDpin LED脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	LED Base LED基座			PC 塑料		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			Aluminum alloy 铝合金		1		Oxidized/Black 氧化/黑色					
1	Key 按键			Aluminum alloy 铝合金		1		Oxidized/Black 氧化/黑色					
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91921G124RA5150		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
					ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						
A		B		C		D		E		F		G	



A4					 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91921G124RA5150
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1						X.X	± 0.15	ROC PU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission.				

	A	B	C	D	E	F	G																																																																	
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制							1																																																																
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜							2																																																																
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1NO/1NO1NC开关、无指示灯功能 5.6线：用于2NO/2NO2NC开关、无指示灯功能 6.5线：用于1NO/1NO1NC、单色指示灯带开关功能 7.8线：用于2NO/2NO2NC、单色指示灯带开关功能 8.6线：用于1NO/1NO1NC、双色指示灯带开关功能 9.7线：用于1NO/1NO1NC、三色或220v双色指示灯带开关功能							3																																																																
4								4																																																																
5	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width:5%;">A4</td> <td style="width:10%;"></td> <td style="width:15%;"></td> <td style="width:10%;"></td> <td rowspan="5" style="text-align: center; vertical-align: middle;">  台普 ROCPCU </td> <td colspan="2" style="text-align: center;">COMMON TOLERANCE</td> <td style="text-align: center;">UNIT</td> <td style="text-align: center;">MM</td> <td style="text-align: center;">PROJECTED</td> <td style="text-align: center;"></td> <td style="text-align: center;">PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td></td> <td colspan="2"></td> <td style="text-align: center;">DRAWN BY</td> <td style="text-align: center;">FUYUAN</td> <td style="text-align: center;">CHECKED BY</td> <td style="text-align: center;">COCO</td> <td style="text-align: center;">MODEL NO: TP91921G124RA5150</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td></td> <td style="text-align: center;">X.XX</td> <td style="text-align: center;">± 0.10</td> <td style="text-align: center;">DATE</td> <td style="text-align: center;">2019</td> <td style="text-align: center;">APPROVAL B</td> <td style="text-align: center;">ALEN</td> <td style="text-align: center;">Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td></td> <td style="text-align: center;">X.X</td> <td style="text-align: center;">± 0.15</td> <td colspan="5" rowspan="2" style="text-align: center; vertical-align: middle;"> ROCPCU TECHNOLOGY CO.,LTD </td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> <td style="text-align: center;">X</td> <td style="text-align: center;">± 0.25</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td style="text-align: center;">ANGULAR</td> <td style="text-align: center;">—</td> <td colspan="5" style="text-align: center; font-size: small;">Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</td> </tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91921G124RA5150	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission					5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																													
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91921G124RA5150																																																													
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																													
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD																																																																	
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						± 0.25																																																												
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission																																																																	
	A	B	C	D	E	F	G																																																																	

1



3

- 4

4

- 5

5