



面板最大厚度9.30 [0.366]



Single color electrical schematic diagram
单色电气原理图



Installation View
安装视图

A4				 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92207G124RS
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
					X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G				
1	性能参数				13. Electrical life: 100000 cycles						
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A				电气寿命: 100000 cycles						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V				14. mechanical: 500000cycles						
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min				机械寿命: 500000cycles						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ				15. Operation method:Self-locking						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ				操作方式: 自锁式						
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10				16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10				17. LED lamp lifespan: 40000h LED寿命: 40000h						
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N				18. LED color: Red LED颜色: 红色						
	9. Protection level:IP67 防护等级:IP67				19. LED Lamp Voltage: 24V LED灯电压: 24V						
2	10. Explosion prevention level: IK10 防暴等级: IK10				20. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃										
	12. Compression torque: ≤ 4N 按压扭力: ≤4N										
	连接形式										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
	2. Can be used with dedicated connectors: 可配专用接插件使用:										
	2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)										
	2.2 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极										
3											
4											
5											
A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92207G124RS
A2					X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocps.tw
A1					X.X ± 0.15		ROCPS TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X ± 0.25						
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
					C	D	E	F	G		



COMMON TOLERANCE

X.XX ± 0.10

X.X ± 0.15

X ± 0.25

ANGULAR —

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP92207G124RS

DATE

2019

APPROVAL B

ALEN

Https: www.roc pu.tw

ROC PU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G																																																																
1	材质参数 <table border="1"> <tr> <td>10</td><td>luminous zone 发光区</td><td>PC 塑胶</td><td>1</td><td></td></tr> <tr> <td>9</td><td>LEDpin LED引脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>8</td><td>Base 底座</td><td>PA46</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>gold-plating 镀金</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>silver alloy 银合金</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>5</td><td>LED Base LED基座</td><td>PC 塑胶</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>1</td><td>Key 按键</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>							10	luminous zone 发光区	PC 塑胶	1		9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银	8	Base 底座	PA46	1		7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银	5	LED Base LED基座	PC 塑胶	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	SUS 不锈钢	1		1	Key 按键	SUS 不锈钢	1		NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1								
10	luminous zone 发光区	PC 塑胶	1																																																																				
9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银																																																																			
8	Base 底座	PA46	1																																																																				
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金																																																																			
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银																																																																			
5	LED Base LED基座	PC 塑胶	1																																																																				
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																			
3	Oring O型圈	Silica gel 硅胶	1																																																																				
2	Housing 外壳	SUS 不锈钢	1																																																																				
1	Key 按键	SUS 不锈钢	1																																																																				
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																			
2								2																																																															
3								3																																																															
4								4																																																															
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td colspan="3">MODEL NO: TP92207G124RS</td></tr> <tr> <td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td colspan="3">Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td><td colspan="7" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td>ANGULAR</td><td>—</td><td colspan="6">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92207G124RS			A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			A1				ROCPCU TECHNOLOGY CO.,LTD							REV	DATE	REVISION	DESCRIPTION	ISSUE						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																												
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92207G124RS																																																														
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																														
A1					ROCPCU TECHNOLOGY CO.,LTD																																																																		
REV	DATE	REVISION	DESCRIPTION									ISSUE																																																											
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																
	A	B	C	D	E	F	G																																																																