


## SMD Crystal Oscillator 2.0 ×1.6 mm

### Feature

- Typical 2.05 x 1.65 x 0.75 mm SMD package.
- Tight symmetry (45 to 55%) available.
- Operation voltage: 1.8V, 2.5V, 3.3V
- Tri-state enable/disable
- RoHS compliant/Pb-free




### Electrical Specifications

Parameter	3.3V		2.5V		1.8V		Unit
	Min.	Max.	Min.	Max.	Min.	Max.	
Supply Voltage Variation	2.97	3.63	2.25	2.75	1.62	1.98	V
Frequency Range	1.5	50	1.5	50	1.5	50	MHz
Standard Frequency			24,26,32,40				MHz
Supply Current	-	15	-	10	-	7	mA
Duty Cycle	45	55	45	55	45	55	%
Transition Time : Rise/Fall Time	1.5 MHz $\leq$ FO < 20MHz 20 MHz $\leq$ FO < 50MHz	-	4	-	4	-	5
Output Level (CMOS)	Output High(Logic "1") Output Low(Logic "0")	2.97		2.25		1.62	
Start Time	-	2	-	2	-	2	mSec
Tri-State (Input to Pin 1)	Enable(High Voltage or floating) Disable(Low Voltage or GND)	2.31	-	1.75	-	1.26	
Period Jitter (Pk-Pk)	-	40	-	40	-	40	pSec
RMS Phase Jitter (integrated 12kHz to 20MHz)	-	1	-	1	-	1	pSec
Standby Current	-	10	-	10	-	10	$\mu$ A
Aging(@25 1st year)	-	$\pm 3$	-	$\pm 3$	-	$\pm 3$	ppm
Storage Temp. Range	-55	125	-55	125	-55	125	°C


Standard frequencies are frequencies which the crystal has been designed and does not imply a stock position

.+ Transition times are measured between 10% and 90% of VDD, with an output load of 15pF.

### Dimension(mm)



### Solder Pad Layout(mm)



To ensure optimal oscillator performance, place a by-pass capacitor of 0.1  $\mu$ F as close to the part as possible between Vdd and GND pads.

### FREQ. STABILITY vs. TEMP. RANGE

Temp. (°C)	±20	±25	±50
-10 ~ +60	○	○	○
-20 ~ +70	△	○	○
-40 ~ +85	X	○	○
-40 ~ +125	X	X	○

○: Available △ :Conditional X: Not available

Inclusive of calibration @ 25 °C, operating temperature range, input voltage variation, load variation, aging (1st year), shock, and vibration