




A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93006P224RA
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

	A		B		C		D		E		F		G
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A												
	2. Rated current:3A/DC36V 额定电流:3A/DC36V												
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min												
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ												
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ												
	6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10												
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10												
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃												
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration												
2	10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	11. Protection level:IP67 防护等级:IP67												
	12. Explosion prevention level: IK10 防暴等级: IK10												
	13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
	14. Compression torque: ≤ 3.5N 按压扭力: ≤3.5N												
	15. Electrical life: 500000 cycles 电气寿命: 500000 cycles												
	16. mechanical: 500000cycles 机械寿命: 500000cycles												
	17. Operation method:Self repeating form 操作方式: 自复式												
	18. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下												
	19. LED lamp lifespan: 40000h LED寿命: 40000h												
3	20. LED color: Red LED颜色: 红色												
	21. LED Lamp Voltage: 24V LED灯电压: 24V												
	22. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N												
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 1NO1NCSwitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)												
	2.2 2NO2NC Switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC) 2NO2NC开关功能线材: 绿黑线(C)、蓝黑线 (NO)、黄白先 (NC)												
	2.2 LED Functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极												
4	A4					COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:	
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93006P224RA	
	A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
	A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					
	REV	DATE	REVISION	DESCRIPTION		ISSUE	X						
						ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					

	A	B	C	D	E	F	G
1	材质参数						
	10	luminous zone 发光区	PC 塑胶	1			
	9	LEDpin LED引脚	Brass 黄铜	1	gold-plating 镀金		
	8	Base 底座	PA46	1			
	7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金		
	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银		
	5	LED Base LED基座	PC 塑胶	1			
	4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍		
	3	Oring O型圈	Silica gel 硅胶	1			
2	2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色		
	1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色		
	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注		
3							
4							

A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93006P224RA
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION DESCRIPTION	ISSUE		ANGULAR	—					
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission											