


A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91929P224RA5150
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
					X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	_____		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission		

A				B		C		D		E		F		G		
1	性能参数															
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A															
	2. Rated current:3A/DC36V 额定电流:3A/DC36V															
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min															
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ															
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ															
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10															
	7. Contact stroke:1.00mm±0.10 接触行程 :1.00mm±0.10															
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N															
	9. Protection level:IP67 防护等级:IP67															
2	10. Explosion prevention level: IK10 防暴等级: IK10															
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃															
	12. Compression torque: ≤ 4N 按压扭力: ≤4N															
	13. Electrical life: 500000 cycles 电气寿命: 500000 cycles															
	14. mechanical: 500000cycles 机械寿命: 500000cycles															
	15. Operation method:Self repeating form 操作方式: 自复式															
	16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N															
	17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下															
	18. LED lamp lifespan: 40000h LED寿命: 40000h															
	19. LED color: Red LED颜色: 红色															
3																
4	连接形式															
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下															
	2. Can be used with dedicated connectors: 可配专用接插件使用:															
	2.1 Switch function wire: Blue wire (NO) 开关功能线材: 蓝线 (NO)															
5	A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:				
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91929P224RA5150				
	A2							DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw				
	A1							ROC PU TECHNOLOGY CO.,LTD								
	REV	DATE	REVISION	DESCRIPTION												ISSUE
									Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission							
	A				B		C		D		E		F		G	

1					2					3					4									
材质参数																								
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金				
6					Contact material 接触材质					silver alloy 银合金					1					Silvering 镀银				
5					Base 基座					PA66					1									
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍				
3					Oring O型圈					Silica gel 硅胶					1									
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色				
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色				
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注				

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91929P224RA5150
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission											



性能参数

- 1.L1-导线长度：默认150MM长；
- 2.L2-线头长度：默认10MM
- 3.L3-剥头长度：默认3MM
- 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM
- 5.线型拉力N：（0.15-0.25MM²）≤30N、（0.3MM²）≤40N、（0.5MM²）≤50N、（0.75MM²）≤60N
- 6.需要其他线长、线型、可以定

材质参数


- 1.插壳：浅蓝色尼龙胶壳
- 2.端子：磷铜y镀锡色
- 3.导电线材：紫铜

线束使用说明

- 1.2线：用于单色指示灯、无开关功能
- 2.2线：用于1NO开关、无指示灯功能
- 3.4线：用于1NO开关、单色指示灯带灯开关功能

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91929P224RA5150
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

19MM系列单色按钮开关接线说明



接线说明:

- 1、供电电源的负极、设备的负极、按钮开关的LED负极，并接一起。
- 2、供电电源的正极，按钮开关的一只NO脚，并接一起。
- 3、设备的正极，按钮开关的另外一只NO脚、按钮开关的LED正极，并接一起。

实现功能:

- 1、按钮开关**按下去**时: 设备**通电**, 按钮开关LED**灯亮**。
- 2、按钮开关**按回去**时: 设备**断电**, 按钮开关LED**灯灭**。

注: 说明图的电压为接线参考使用, 电源电压根据实际供电电压为准。

红线为正极 (火线)
黑线为负极 (零线)

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				