





A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94006P224RA5150
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. Compression torque: ≤ 2.5N 按压扭力: ≤2.5N						
	3. Power-frequency withstand voltage:2000V/1min 工频耐压:2000V/1min						15. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. Mechanical: 500, 000cycles 机械寿命: 500,000cycles						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. Operation method:self repeating form 操作方式: 自复式						
	6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10						18. LED lamp power consumption: 20mA以下 LED灯功耗: 20mA以下						
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10						19. LED lamp lifespan: 40000h LED寿命: 40000h						
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃						20. LED color: Red LED颜色: 红色						
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration						21. LED Lamp Voltage: 24V LED灯电压: 24V						
	10. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m						22. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	11. Protection level:IP67 防护等级:IP67												
2	12. Explosion prevention level: IK10 防暴等级: IK10												
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 Switch function wire: Green Line (C) Blue Line (NO) Yellow Line (NC) 开关功能线材: 绿线 (C) 蓝线 (NO) 黄线 (NC)												
	2.2 LED functional wire: red wire positive pole black wire negative pole LED功能线材: 红线正极 黑线负极												
	2.3 LED is an electrodeless lamp bead that can be lit without the need to separate positive and negative poles LED为无极灯珠, 无需分正负极也可点亮												


材质参数												



A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94006P224RA5150
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw		
A1					ROC PU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION								
					X.XX	± 0.10	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
					X.X	± 0.15					
					X	± 0.25					
					ANGULAR	——					

	A	B	C	D	E	F	G																																																	
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制						1																																																	
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜						2																																																	
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1N0/1N01NC开关、无指示灯功能 5.6线：用于2N0/2N02NC开关、无指示灯功能 6.5线：用于1N0/1N01NC、单色指示灯带开关功能 7.8线：用于2N0/2N02NC、单色指示灯带开关功能 8.6线：用于1N0/1N01NC、双色指示灯带开关功能 9.7线：用于1N0/1N01NC、三色或220v双色指示灯带开关功能						3																																																	
4							4																																																	
5	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width:5%;">A4</td> <td style="width:10%;"></td> <td style="width:10%;"></td> <td style="width:10%;"></td> <td rowspan="5" style="width:10%; text-align:center; vertical-align: middle;">  台普 ROCPCU </td> <td style="width:10%;">COMMON TOLERANCE</td> <td style="width:10%;">UNIT</td> <td style="width:10%;">MM</td> <td style="width:10%;">PROJECTED</td> <td style="width:10%; text-align:center;">  </td> <td style="width:20%;">PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td></td> <td></td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO: TP94006P224RA5150</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td></td> <td></td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td>Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td></td> <td></td> <td>X</td> <td>± 0.25</td> <td colspan="3" rowspan="2" style="text-align:center; font-size: 24px; font-weight: bold;">ROCPCU TECHNOLOGY CO.,LTD</td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> <td>ANGULAR</td> <td>—</td> </tr> </table> Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission							A4				 台普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:	A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94006P224RA5150	A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD			REV	DATE	REVISION	DESCRIPTION	ISSUE	ANGULAR	—	5
A4				 台普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:																																														
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94006P224RA5150																																														
A2						DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																														
A1						X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD																																																
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	—																																																	
	A	B	C	D	E	F	G																																																	

40MM系列双排单色按钮开关接线说明



接线说明:

- 1、供电电源的正极、按钮开关左边的C脚，接一起。
- 2、供电电源的负极，按钮开关右边的C脚，接一起。
- 3、设备的正极，按钮开关的左NO脚、按钮开关的LED正极，并接一起。
- 4、设备的负极，按钮开关的右NO脚、按钮开关的LED负极，并接一起。

实现功能:

- 1、按钮开关按下去时: 设备正负极都通电, 按钮开关LED灯亮。
- 2、按钮开关按回去时: 设备正负极都断电, 按钮开关LED灯灭。

注: 说明图的电压为接线参考使用, 电源电压根据实际供电电压为准。

红线为正极 (火线)

黑线为负极 (零线)

A4					 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				