




A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. Compression torque: ≤ 2.5N 按压扭力: ≤2.5N						
	3. Power-frequency withstand voltage:2000V/1min 工频耐压:2000V/1min						15. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. Mechanical: 500, 000cycles 机械寿命: 500,000cycles						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. Operation method:self repeating form 操作方式: 自复式						
	6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10						18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10												
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃												
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration												
2	10. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m												
	11. Protection level:IP67 防护等级:IP67												
	12. Explosion prevention level: IK10 防暴等级: IK10												
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 Switch function wire: Green Line (C) Blue Line (NO) Yellow Line (NC) 开关功能线材: 绿线 (C) 蓝线 (NO) 黄线 (NC)												

A		B		C		D		E		F		G	
材质参数													
9													
8													
7	Base 底座		PA46		1					Silvering 镀银			
6	NOPin NO引脚		Brass 黄铜		1					gold-plating 镀金			
5	Contact material 接触材质		silver alloy 银合金		1					Silvering 镀银			
4	Arm nut 固定螺帽		Brass 黄铜		1					nickeling 镀镍			
3	Oring O型圈		Silica gel 硅胶		1								
2	Housing 外壳		SUS 不锈钢		1								
1	Key 按键		SUS 不锈钢		1								
NO 序号	Part name 部件名		Material 材料		QTY 数量					Remark 备注			

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94001P2S		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROC CPU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION								ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission	
A		B		C		D		E		F		G	

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission