




A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Electrical life: 500000 cycles 电气寿命: 500000 cycles						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. mechanical: 500000cycles 机械寿命: 500000cycles						
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min						15. Operation method:Self-locking 操作方式: 自锁式						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ												
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10												
	7. Contact stroke:1.00mm±0.10 接触行程 :1.00mm±0.10												
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	9. Protection level:IP67 防护等级:IP67												
2													
	10. Explosion prevention level: IK09 防暴等级: IK09												
	11. Working environment temperature: -20 ℃~-+55 ℃ 工作环境温度: -20 ℃~-+55 ℃												
	12. Compression torque: ≤ 4N 按压扭力: ≤4N												
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 Switch function wire: blue wire (NO) 开关功能线材: 蓝线 (NO)												

	A	B	C	D	E	F	G
1	材质参数						1
2	7	Pin 引脚	Brass 黄铜	1	Silvering 镀银		2
	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银		
	5	Base 基座	PA66	1			
3	4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍		3
	3	Oring O型圈	Silica gel 硅胶	1			
	2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色		
4	1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色		4
	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注		

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91928G1A
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					

A	B	C	D	E	F	G
---	---	---	---	---	---	---

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission