



ROHS compliant



NOTES:

1.Specification:

- 1> Operation force: 500gf Max.
- 2> Operation Temperature: -30℃ to +85℃.
- 3> Storage Temperature: -40℃ to +85℃.
- 4> Mechanical Life: 3000 cycles operations.
- 5> Resistance to Soldering: 260±5℃ for 3-5 Seconds.

2.PLATING:


- 1> GOLD flash 1u" (min) SOLDERTAIL, 3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1> Non-switch Rating: 100mA at 50V DC.
- 2> Switching Rating: 25mA at 24V DC.
- 3> Contact Resistance: Initial 50mΩ Max. Contact Resistance: After life 100mΩ Max.
- 4> Insulation Resistance: 1000MΩ Min at 500VDC.
- 5> Dielectric Strength: 500V AC for 60seconds.
- 6> Switch Capacitance: 5PF Max at 1MHZ.



4.PART NUMBER DESCRIPTION:

DSPV XX L S G E T



5.PACKAGE: 35pcs/Tube, 1400pcs/Box.

REV.	ECN NO.	DRAWN	DATE



东莞市康深电子科技有限公司
Kongshen Electronics technology co., LTD.

Drawing	dengk	Date	2012.03.25	LINER	ANGLES	PRODUCT Family	DSPV Series	Pitch	2.54mm
Check	zhong	Scale	4:1			PRAT NO.	DSPV05LSGET		
Approved		Unit	MM			FILE NO.	KE-DSPV-005-S-A		
Size	A4	Rev.	A			PROJECTION			