




A4					 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91915G124RS
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.roc pu.tw
A1						X.X	± 0.15	ROC PU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G																																																								
1	性能参数 1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A 2. Rated current:3A/DC36V 额定电流:3A/DC36V 3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10 7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10 8. welding temperature: 320 °C± 20 °C 焊接温度: 320 °C± 20 °C 9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration 10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 11. Protection level:IP67 防护等级:IP67 12. Explosion prevention level: IK10 防暴等级: IK10 13. Working environment temperature: -20 °C~+55 °C 工作环境温度: -20 °C~+55 °C 14. Compression torque: ≤ 4N 按压扭力: ≤4N 15. Electrical life: 500000 cycles 电气寿命: 500000 cycles 16. mechanical: 500000cycles 机械寿命: 500000cycles 17. Operation method:Self-locking 操作方式: 自锁式 18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 20. LED lamp lifespan: 40000h LED寿命: 40000h 21. LED color: Red LED颜色: 红色																																																														
2																																																															
3																																																															
4	连接形式 1. Welding temperature of wire: 320 ± 20 °C 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 2. Can be used with dedicated connectors: 可配专用接插件使用: 2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC) 2.2 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极																																																														
5																																																															
<table><tr><td>A4</td><td></td><td></td><td></td><td rowspan="5"> 台普 ROCPU </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr><tr><td>A3</td><td></td><td></td><td></td><td>X.XX</td><td>± 0.10</td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td>MODEL NO: TP91915G124RS</td></tr><tr><td>A2</td><td></td><td></td><td></td><td>X.X</td><td>± 0.15</td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td>Https: www.rocpu.tw</td></tr><tr><td>A1</td><td></td><td></td><td></td><td>X</td><td>± 0.25</td><td colspan="5" rowspan="2">ROCPU TECHNOLOGY CO.,LTD</td></tr><tr><td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td><td>ANGULAR</td><td colspan="5">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr></table>								A4				台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91915G124RS	A2				X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw	A1				X	± 0.25	ROCPU TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
A4				台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																				
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91915G124RS																																																				
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw																																																				
A1					X	± 0.25	ROCPU TECHNOLOGY CO.,LTD																																																								
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR						Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																			
	A	B	C	D	E	F	G																																																								

	A	B	C	D	E	F	G																																																																
1	材质参数 <table border="1"> <tr> <td>10</td><td>luminous zone 发光区</td><td>PC 塑料</td><td>1</td><td></td></tr> <tr> <td>9</td><td>LEDpin LED脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>8</td><td>Base 底座</td><td>PA46</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>gold-plating 镀金</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>silver alloy 银合金</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>5</td><td>LED Base LED基座</td><td>PC 塑料</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>1</td><td>Key 按键</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>							10	luminous zone 发光区	PC 塑料	1		9	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银	8	Base 底座	PA46	1		7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银	5	LED Base LED基座	PC 塑料	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	SUS 不锈钢	1		1	Key 按键	SUS 不锈钢	1		NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1								
10	luminous zone 发光区	PC 塑料	1																																																																				
9	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银																																																																			
8	Base 底座	PA46	1																																																																				
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金																																																																			
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银																																																																			
5	LED Base LED基座	PC 塑料	1																																																																				
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																			
3	Oring O型圈	Silica gel 硅胶	1																																																																				
2	Housing 外壳	SUS 不锈钢	1																																																																				
1	Key 按键	SUS 不锈钢	1																																																																				
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																			
2								2																																																															
3								3																																																															
4								4																																																															
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td colspan="3">MODEL NO: TP91915G124RS</td></tr> <tr> <td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td colspan="3">Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td><td colspan="7" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91915G124RS			A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			A1				ROCPCU TECHNOLOGY CO.,LTD							REV	DATE	REVISION	DESCRIPTION	ISSUE														5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																												
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91915G124RS																																																														
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																														
A1					ROCPCU TECHNOLOGY CO.,LTD																																																																		
REV	DATE	REVISION	DESCRIPTION									ISSUE																																																											
	A	B	C	D	E	F	G																																																																