





	A	B	C	D	E	F	G				
1	性能参数				13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A				14. Compression torque: ≤ 2.5N 按压扭力: ≤2.5N						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V				15. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles						
	3. Power-frequency withstand voltage:2000V/1min 工频耐压:2000V/1min				16. Mechanical: 500, 000cycles 机械寿命: 500,000cycles						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ				17. Operation method:self repeating form 操作方式: 自复式						
2	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ				18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10										
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10										
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃										
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration										
	10. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m										
	11. Protection level:IP67 防护等级:IP67										
3	12. Explosion prevention level: IK10 防暴等级: IK10										
	连接形式										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
	2. Can be used with dedicated connectors: 可配专用接插件使用:										
4	2.1 Switch function wire: Green Line (C) Blue Line (NO) Yellow Line (NC) 开关功能线材: 绿线 (C) 蓝线 (NO) 黄线 (NC)										
5	A4			 台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP94001P2S5150
	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
	A1				X.X	± 0.15	ROCPU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION		ISSUE	X					
					ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission.					
	A	B	C	D	E	F	G				


A		B		C		D		E		F		G	
材质参数													
9													
8													
7	Base 底座			PA46			1			Silvering 镀银			
6	NOPin NO引脚			Brass 黄铜			1			gold-plating 镀金			
5	Contact material 接触材质			silver alloy 银合金			1			Silvering 镀银			
4	Arm nut 固定螺帽			Brass 黄铜			1			nickeling 镀镍			
3	Oring O型圈			Silica gel 硅胶			1						
2	Housing 外壳			SUS 不锈钢			1						
1	Key 按键			SUS 不锈钢			1						
NO 序号	Part name 部件名			Material 材料			QTY 数量			Remark 备注			

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94001P2S5150		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROC CPU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
A		B		C		D		E		F		G	



	A	B	C	D	E	F	G																																																																				
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制							1																																																																			
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜							2																																																																			
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1N0/1N01NC开关、无指示灯功能 5.6线：用于2N0/2N02NC开关、无指示灯功能 6.5线：用于1N0/1N01NC、单色指示灯带开关功能 7.8线：用于2N0/2N02NC、单色指示灯带开关功能 8.6线：用于1N0/1N01NC、双色指示灯带开关功能 9.7线：用于1N0/1N01NC、三色或220v双色指示灯带开关功能							3																																																																			
4								4																																																																			
5	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width:5%;">A4</td> <td style="width:10%;"></td> <td style="width:10%;"></td> <td style="width:10%;"></td> <td rowspan="5" style="width:10%; text-align: center;">  </td> <td style="width:10%;">COMMON</td> <td style="width:10%;">TOLERANCE</td> <td style="width:10%;">UNIT</td> <td style="width:10%;">MM</td> <td style="width:10%;">PROJECTED</td> <td style="width:10%; text-align: center;">  </td> <td style="width:20%;">PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO: TP94001P2S5150</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td></td> <td></td> <td>X.XX</td> <td>± 0.10</td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td>Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td></td> <td></td> <td>X.X</td> <td>± 0.15</td> <td colspan="5" rowspan="2" style="text-align: center; font-size: 24px; font-weight: bold;">ROC CPU TECHNOLOGY CO.,LTD</td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> <td>X</td> <td>± 0.25</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td>ANGULAR</td> <td>——</td> <td colspan="5" style="font-size: 10px;">Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</td> </tr> </table>							A4					COMMON	TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94001P2S5150	A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25						ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission					5
A4					COMMON	TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:																																																																
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO		MODEL NO: TP94001P2S5150																																																														
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN		Https: www.rocpcu.tw																																																														
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD																																																																			
REV	DATE	REVISION	DESCRIPTION		ISSUE	X	± 0.25																																																																				
					ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission																																																																				
	A	B	C	D	E	F	G																																																																				

40MM系列单排无灯按钮开关接线说明



接线说明:

- 1、供电电源的负极、设备的负极，并接一起。
- 2、供电电源的正极，按钮开关的C脚，并接一起。
- 3、设备的正极，按钮开关的NO脚，并接一起。

实现功能:

- 1、按钮开关**按下去**时：设备**通电**。
- 2、按钮开关**按回去**时：设备**断电**。

注：说明图的电压为接线参考使用，电源电压根据实际供电电压为准。

红线为正极（火线）

黑线为负极（零线）

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				