

MBRB30100CT

30A SCHOTTKY BARRIER RECTIFIER

General Description

MBRB30100CT Device optimized for ultra-low forward voltage drop to maximize efficiency in Power Supply applications. The device is intended for use in Switched Mode Power Supplies (SMPS), adapters and DC/DC converters.

Features

- Low forward voltage
- Low power loss/ high efficiency
- High Surge Current Capability
- RoHS Compliant


Product Summary

V _{RRM}	V _F	I _{F(AV)}
100V	0.88V	30A

Applications

- DC/DC converter
- Switched Mode Power Supplies (SMPS)
- Low Voltage High Frequency Invers Circuit

TO-263 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{RRM}	Peak Repetitive Reverse Voltage	100	V
I _{F(AV)}	Average Rectified Forward Current (Rated VR-20Khz Square Wave) - 50% duty cycle	15 (Per Leg) 30 (Total)	A
dv/dt	Voltage rate of change (Rated VR)	10000	V/uS
I _{RRM}	Peak Repetitive Reverse Surge Current (2uS,1Khz)	0.5	A
I _{FSM}	Forward Peak Surge Current(Rated Load 8.3ms Half Mssine Wave-According to JEDEC Method)	350x2	A
T _J , T _{STG}	Operating and Storage Temperature Range	-40 to 150	°C


Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJC}	Thermal Resistance, Junction to Case(Per Leg)	2	---	°C/W


Electrical Characteristics

ymbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
V _F	Forward Voltage Drop per diode	I _F =15A, T _C =25°C	---	0.81	0.88	V
		I _F =15A, T _C =125°C	---	---	0.75	
I _R	Reverse Leakage Current per diode	V _R =100V, T _C =25°C	---	---	0.05	mA
		V _R =100V, T _C =125°C	---	---	10	mA


Typical Performance Characteristics



Current derating curve, per element



The forward voltage and forward current curve



The reverse leak current and the reverse voltage (single-device) curve

This product has been designed and qualified for the consumer market.
 Cmos assumes no liability for customers' product design or applications.
 Cmos reserves the right to improve product design, functions and reliability without notice.