




REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	20.04.28	Mark
A1	所有材料铅含量小于1000PPM	20.10.26	S.He

1. Electrical Characteristics
- 1.1 Impedance: 50 Ohm

1.2 Working Frequency: DC - 3 GHz

1.3 S.W.R.: ≤1.5

1.4 Working Voltage:335V / max

1.5 Insulation Resistance: 5000 Mohm

1.6 Contact Resistance: Center Contact:3mohm

1.7 Outer Contact: ≤2 mohm
- 2.Environmental
- 2.1 Working Temperature Range: - 55 。C~ +125。C

所有材料铅含量小于1000PPM			
5	INSULATOR_2	PTFE, WHITE	1
4	BODY_2	BRASS, GOLD	1
3	BODY_1	BRASS, GOLD	1
2	INSULATOR_1	PTFE, WHITE	1
1	CENTER CONTACT	FEMALE, BRASS, GOLD	1
No.	PART NAME	SPECIFICATION DESCRIPTION	Q'TY

GENERAL TOLERANCE: LINEAR: X ±0.30 X.X ±0.20 X.XX ±0.15 X.XXX ±0.10 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司	
FILE NAME: 零件图		TITLE: 射频连接器组件	
ENG/DATE: Mark/20.04.28		90度SMA母头母针FOR PCB, 镀金	
CHE/DATE:		SQ7.0*L16.8*H13.8, 脚长3.7mm, 针OD:1.27mm	
APP/DATE:		P/N: 2LC15SF101	
UNIT: mm		SCALE: 1:1	REVISION: A0
			SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ☒RoHS; ☐HF; ☐SONY SS-00259; ☐OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE