





A		B		C		D		E		F		G	
性能参数													
1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A													
2. Rated current:3A/DC36V 额定电流:3A/DC36V													
3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min													
4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ													
5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ													
6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10													
7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10													
8. welding temperature: 320 °C± 20 °C 焊接温度: 320 °C± 20 °C													
9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration													
10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N													
11. Protection level:IP67 防护等级:IP67													
12. Explosion prevention level: IK10 防暴等级: IK10													
13. Working environment temperature: -20 °C~+55 °C 工作环境温度: -20 °C~+55 °C													
14. Compression torque: ≤ 4N 按压扭力: ≤ 4N													
15. Electrical life: 100000 cycles 电气寿命: 100000 cycles													
16. mechanical: 500000cycles 机械寿命: 500000cycles													
17. Operation method:Self-locking 操作方式: 自锁式													
18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N													
连接形式													
1. Welding temperature of wire: 320 ± 20 °C 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下													
2. Can be used with dedicated connectors: 可配专用接插件使用:													
2.1 Switch function wire: Green line (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿线 (C) 蓝线 (NO) 黄线 (NC)													
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92203G1A5150		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION										
A		B		C		D		E		F		G	


A		B		C		D		E		F		G	
材质参数													
8		Base 底座		PA46		1							
7		Pin 引脚		Brass 黄铜		1				gold-plating 镀金			
6		Contact material 接触材质		silver alloy 银合金		1				Silvering 镀银			
5		LED Base LED基座		PC 塑料		1							
4		Arm nut 固定螺帽		Brass 黄铜		1				nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶		1							
2		Housing 外壳		Aluminum alloy 铝合金		1				Oxidized/Black 氧化/黑色			
1		Key 按键		Aluminum alloy 铝合金		1				Oxidized/Black 氧化/黑色			
NO 序号		Part name 部件名		Material 材料		QTY 数量				Remark 备注			

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92203G1A5150
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					



	A	B	C	D	E	F	G																																																																				
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制							1																																																																			
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜							2																																																																			
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1N0/1N01NC开关、无指示灯功能 5.6线：用于2N0/2N02NC开关、无指示灯功能 6.5线：用于1N0/1N01NC、单色指示灯带开关功能 7.8线：用于2N0/2N02NC、单色指示灯带开关功能 8.6线：用于1N0/1N01NC、双色指示灯带开关功能 9.7线：用于1N0/1N01NC、三色或220v双色指示灯带开关功能							3																																																																			
4								4																																																																			
5	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width:5%;">A4</td> <td style="width:10%;"></td> <td style="width:10%;"></td> <td style="width:10%;"></td> <td rowspan="5" style="text-align:center; vertical-align: middle;">  台普 ROC CPU </td> <td style="width:10%;">COMMON</td> <td style="width:10%;">TOLERANCE</td> <td style="width:10%;">UNIT</td> <td style="width:10%;">MM</td> <td style="width:10%;">PROJECTED</td> <td style="width:10%; text-align:center;">  </td> <td style="width:20%;">PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO:TP92203G1A5150</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td></td> <td></td> <td>X.XX</td> <td>± 0.10</td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td>Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td></td> <td></td> <td>X.X</td> <td>± 0.15</td> <td colspan="5" rowspan="2" style="text-align:center; font-size: 24px; font-weight: bold;">ROC CPU TECHNOLOGY CO.,LTD</td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> <td>X</td> <td>± 0.25</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td>ANGULAR</td> <td>——</td> <td colspan="5" style="font-size: 10px;">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td> </tr> </table>							A4				 台普 ROC CPU	COMMON	TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP92203G1A5150	A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25						ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					5
A4				 台普 ROC CPU	COMMON	TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:																																																																
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO		MODEL NO:TP92203G1A5150																																																														
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN		Https: www.rocpcu.tw																																																														
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD																																																																			
REV	DATE	REVISION	DESCRIPTION		ISSUE	X	± 0.25																																																																				
					ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																				
	A	B	C	D	E	F	G																																																																				

22MM系列单排无灯按钮开关接线说明



接线说明:

- 1、供电电源的负极、设备的负极，并接一起。
- 2、供电电源的正极，按钮开关的C脚，并接一起。
- 3、设备的正极，按钮开关的NO脚，并接一起。

实现功能:

- 1、按钮开关**按下去**时：设备**通电**。
- 2、按钮开关**按回去**时：设备**断电**。

注：说明图的电压为接线参考使用，电源电压根据实际供电电压为准。

红线为正极（火线）
黑线为负极（零线）

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALAN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				