




	A	B	C	D	E	F	G
1	性能参数				12. Explosion prevention level: IK10 防暴等级: IK10		
	1. Heating current: Ui: AC250V, Ith: 20A 发热电流: Ui: AC250V, Ith: 20A				13. Working environment temperature: -40 ℃~+80 ℃ 工作环境温度: -40 ℃~+80 ℃		
	2. Rated current:16A,AC110V/220V 16A,DC12V/24V 额定电流:16A,AC110V220V 16A,DC12V/24V				14. Compression torque: ≤ 4.0N 按压扭力: ≤4.0N		
	3. Power-frequency withstand voltage:1500V/1min 工频耐压:1500V/1min				15. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles		
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ				16. Mechanical: 500, 000cycles 机械寿命: 500,000cycles		
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ				17. Operation method:self-locking 操作方式: 自锁式		
	6. Pressing stroke:3.50mm ± 0.10 按压行程:3.50mm ± 0.10				18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N		
	7. Contact stroke:1.35mm±0.10 接触行程 :1.35mm±0.10						
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃						
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration						
2	10. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m						
	11. Protection level:IP67 防护等级:IP67						
	连接形式						
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下						
	2. Can be used with dedicated connectors: 可配专用接插件使用:						
	2.1 Switch function wire: Blue wire (NO) (1.0²mm) 开关功能线材: 蓝线 (NO) (1.0²mm)						
3							
4							
5							
				Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			
				</			

A		B		C		D		E		F		G	
材质参数													
9													
8													
7		Base 底座		PBT				1		Silvering 镀银			
6		NOPin NO引脚		Brass 黄铜				1		gold-plating 镀金			
5		Contact material 接触材质		silver alloy 银合金				1		Silvering 镀银			
4		Arm nut 固定螺帽		Brass 黄铜				1		nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶				1					
2		Housing 外壳		SUS 不锈钢				1					
1		Key 按键		SUS 不锈钢				1					
NO 序号		Part name 部件名		Material 材料				QTY 数量		Remark 备注			

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992206G1S		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROC CPU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
						ANGULAR		—		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			
A		B		C		D		E		F		G	