







A				B				C				D				E				F				G			
1	性能参数																13. Electrical life: 500000 cycles 电气寿命: 500000 cycles										
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A																14. mechanical: 500000cycles 机械寿命: 500000cycles										
	2. Rated current:3A/DC36V 额定电流:3A/DC36V																15. Operation method:Self-locking 操作方式: 自锁式										
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min																16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N										
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ																17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下										
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ																18. LED lamp lifespan: 40000h LED寿命: 40000h										
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10																19. LED color: Red LED颜色: 红色										
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10																										
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N																										
	9. Protection level:IP67 防护等级:IP67																										
2	10. Explosion prevention level: IK10 防暴等级: IK10																										
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃																										
	12. Compression torque: ≤ 6N 按压扭力: ≤6N																										
	连接形式																										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下																										
	2. Can be used with dedicated connectors: 可配专用接插件使用:																										
	2.1 1NO1NCswitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)																										
	2.2 2NO2NC switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC) 2NO2NC开关功能线材: 绿黑线 (C)、蓝黑线 (NO)、黄白线(NC)																										
	2.3 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极																										
3																											
4																											
5																											

A					B					C					D					E					F					G				
材质参数																																		
10					luminous zone 发光区					PC 塑料					1																			
9					LEDpin LED脚					Brass 黄铜					1					Silvering 镀银														
8					Base 底座					PA46					1																			
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					silver alloy 银合金					1					Silvering 镀银														
5					LED Base LED基座					PC 塑料					1																			
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														




A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91922G124RA5150
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					



Function Parameter
功能参数



Installation diagram
安装示意图



A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE




COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP91922G124RA5150
DATE	2019	APPROVAL B	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

	A	B	C	D	E	F	G					
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制							1				
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜							2				
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1N0/1N01NC开关、无指示灯功能 5.6线：用于2N0/2N02NC开关、无指示灯功能 6.5线：用于1N0/1N01NC、单色指示灯带开关功能 7.8线：用于2N0/2N02NC、单色指示灯带开关功能 8.6线：用于1N0/1N01NC、双色指示灯带开关功能 9.7线：用于1N0/1N01NC、三色或220v双色指示灯带开关功能							3				
4								4				
5	A4				台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
	A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91922G124RA5150		
	A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
	A1					X.XX	± 0.10	ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION	ISSUE		X.X	± 0.15					
					X	± 0.25	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
		A		B		C		D	E	F	G	

19MM系列双排单色按钮开关接线说明



接线说明:

- 1、供电电源的正极、按钮开关左边的C脚，接一起。
- 2、供电电源的负极，按钮开关右边的C脚，接一起。
- 3、设备的正极，按钮开关的左NO脚、按钮开关的LED正极，并接一起。
- 4、设备的负极，按钮开关的右NO脚、按钮开关的LED负极，并接一起

实现功能:

- 1、按钮开关**按下去**时: 设备正负极都**通电**，按钮开关LED**灯亮**。
- 2、按钮开关**按回去**时: 设备正负极都**断电**，按钮开关LED**灯灭**。

注: 说明图的电压为接线参考使用，电源电压根据实际供电电压为准。

红线为正极 (火线)
黑线为负极 (零线)

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				