




	A	B	C	D	E	F	G				
1	性能参数										
2	1. Heating current: Ui: AC250V, Ith: 10A 发热电流: Ui: AC250V, Ith: 10A			12. Explosion prevention level: IK10 防暴等级: IK10							
	2. Rated current:10A,AC110V/220V 10A,DC12V/24V 额定电流:10A,AC110V220V 10A,DC12V/24V			13. Working environment temperature: -40 ℃~-+80 ℃ 工作环境温度: -40 ℃~-+80 ℃							
	3. Power-frequency withstand voltage:1500V/1min 工频耐压:1500V/1min			14. Compression torque: ≤ 5.0N 按压扭力: ≤5.0N							
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			15. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles							
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			16. Mechanical: 500, 000cycles 机械寿命: 500,000cycles							
	6. Pressing stroke:4.00mm ± 0.10 按压行程:4.00mm ± 0.10			17. Operation method:self-locking 操作方式: 自锁式							
	7. Contact stroke:1.20mm±0.10 接触行程 :1.20mm±0.10			18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃										
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration										
	10. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m										
	11. Protection level:IP67 防护等级:IP67										
3											
	连接形式										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
	2. Can be used with dedicated connectors: 可配专用接插件使用:										
	2.1 Switch function wire: Blue wire (NO) (1.0²mm) 开关功能线材: 蓝线 (NO) (1.0²mm)										
4											
5	A4			 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP991906G1S
	A2				X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
	A1				X.X ± 0.15		ROC PU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION		ISSUE	X ± 0.25					
					ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A	B	C	D	E	F	G				

A		B		C		D		E		F		G	
材质参数													
9													
8													
7		Base 底座		PBT				1					
6		NOPin NO引脚		Brass 黄铜				1		gold-plating 镀金			
5		Contact material 接触材质		silver alloy 银合金				1					
4		Arm nut 固定螺帽		Brass 黄铜				1		nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶				1					
2		Housing 外壳		SUS 不锈钢				1					
1		Key 按键		SUS 不锈钢				1					
NO 序号		Part name 部件名		Material 材料				QTY 数量		Remark 备注			

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP991906G1S	
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			
A1					ROC CPU TECHNOLOGY CO.,LTD							
REV	DATE	REVISION	DESCRIPTION									ISSUE
					ANGULAR		—		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission			

A		B		C		D		E		F		G	
---	--	---	--	---	--	---	--	---	--	---	--	---	--