








REV.	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
AO			The first edition released	2016.2.1	lwh





装配图



备注:

1. 表面不可有氧化、破损、刮伤等不良
2. 組裝后螺牙本體8KGf拉拔不可鬆動, 3KGf扭力不可旋轉.
3. 標有()的為重點檢驗項目



7	母针	OD2.48*9.80, 黄铜C2680 镀金1u''	1
6	后塞	OD6.03*5.45, 黄铜C2680 镀镍50u''	1
5	绝缘垫片	OD4.10*1.75, 铁氟龙	1
4	华司	OD14.50*1.1, 黄铜C2680 镀镍50u''	1
3	螺母	H14.40*3.00, 黄铜C2680 镀镍50u''	1
2	铁氟龙	OD5.54 *9.88, 铁氟龙	1
1	螺牙本體	OD9.60*20.5, 锌合金 镀镍50u''	1
NO	ITLM	DESCRIPTION	Q'TY

☒ ☐ ☐ ☐
* NO USING RESTRICTED AND BANNED SUBSTANCE

DIM	TOL	DIM	TOL
X.	±0.20	X'	±4.0"
X.X	±0.15	X.X"	±3.0"
X.XX	±0.05	X.XX"	±2.0"
X.XXX	±0.005	X.XXX"	±1.0"

HJ-Tech		东莞市皇捷通讯科技有限公司			
DRAW NO.		DATE	DRAW NAME: RG1.13 TNC母头母针		
DESIGN:	lwh	2016.2.1			
CHECK:			FILE:	P/N NO. 2LC17SF301	
APPROVED:			MODEL:	UNIT: mm	SHEET: N/A
			REV. A0	SCALE N/A	