General Description

The WST02N30 is silicon N-channel Enhanced VDMOSFETs, is obtained by the self-aligned planar Technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. The transistor can be used in various power switching circuit for system miniaturization and higher efficiency.

Product Summery

BVDSS	RDSON	ID
300V	4000mΩ	2.0A

Applications

- Uninterruptible Power Supply(UPS)
- Power Factor Correction (PFC)
- Load Switch

Features

- Advanced high cell density Trench technology
- Super Low Gate Charge
- Excellent Cdv/dt effect decline
- Green Device Available

SOT-23 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	300	V
V_{GS}	Gate-Source Voltage	±20	V
I_D@T_c=25℃	Continuous Drain Current, V_{GS} @ 10V[1]	2.0	A
I_D@T_c=70℃	Continuous Drain Current, V_{GS} @ 10V[1]	1.1	A
I_{DM}	Pulsed Drain Current[2]	12	A
P_D@T_A=25℃	Total Power Dissipation[3]	1.5	W
T_{STG}	Storage Temperature Range	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	℃

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient [1]	---	125	℃/W
$R_{\theta JC}$	Thermal Resistance Junction-Case[1]	---	60	℃/W

Electrical Characteristics (T_J=25℃, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V , I_D=250uA	300	---	---	V
$\triangle BV_{DSS}/\triangle T_J$	BVDSS Temperature Coefficient	Reference to 25℃ , I_D=1mA	---	0.067	---	V/℃
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=10V , I_D=1.5A	---	3.0	4.0	Ω
		V_{GS}=6V , I_D=0.5A	---	4.5	5.5	
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS} , I_D =250uA	2.0	3.0	4.0	V
$\triangle V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	-4.2	---	mV/℃
I_{DSS}	Drain-Source Leakage Current	V_{DS}=300V , V_{GS}=0V , T_J=25℃	---	---	1	uA
I_{DSS}	Drain-Source Leakage Current	V_{DS}=240V , V_{GS}=0V , T_J=125℃	---	---	100	uA
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±20V , V_{DS}=0V	---	---	±100	nA
Q_g	Total Gate Charge (10V)	V_{DS}=240V , V_{GS}=10V , I_D=1A	---	4.4	---	nC
Q_{gs}	Gate-Source Charge		---	0.7	---	
Q_{gd}	Gate-Drain Charge		---	2.0	---	
$T_{d(on)}$	Turn-On Delay Time	V_{DD}=150V , V_{GS}=10V , R_G=25Ω, I_D=1A .	---	18	---	ns
T_r	Rise Time		---	55	---	
$T_{d(off)}$	Turn-Off Delay Time		---	60	---	
T_f	Fall Time		---	55	---	
C_{iss}	Input Capacitance	V_{DS}=25V , V_{GS}=0V , f=1MHz	---	138	---	pF
C_{oss}	Output Capacitance		---	30	---	
C_{rss}	Reverse Transfer Capacitance		---	5.0	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current[1,4]	V_G=V_D=0V , Force Current	---	---	2.0	A
I_{SM}	Pulsed Source Current[2,4]		---	---	12	A
V_{SD}	Diode Forward Voltage[2]	V_{GS}=0V , I_S=1A , T_J=25℃	---	---	1.4	V
t_{rr}	Reverse Recovery Time	IF=1A , dI/dt=100A/μs , T_J=25℃	---	250	---	nS
Q_{rr}	Reverse Recovery Charge		---	1.8	---	. C

Note :
1.The data tested by surface mounted on a 1 inch^2 FR-4 board with 2OZ copper,t<10sec.
2.The data tested by pulsed , pulse width ≦ 300us , duty cycle ≦ 2%
3.The power dissipation is limited by 150℃ junction temperature
4.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

Typical Characteristics

Figure 1. Output Characteristics (T_J = 25ºC)



Figure 2. Body Diode Forward Voltage



Figure 3. Drain Current vs. Temperature



Figure 4. BV_{DSS} Variation vs. Temperature



Figure 5. Transfer Characteristics



Figure 6. On-Resistance vs. Temperature



Figure 7. Capacitance



Figure 8. Gate Charge



Figure 9. Transient Thermal Impedance



Attention

1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.

2,Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.

3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

5,In the event that any or all Winsok power products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement,etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you Intend to use.

9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.