


ROHS compliant



NOTES:

1.Specification :

- 1>. Operation force: 500gf Max.
- 2>. Operation Temperature: -30 ℃ to+85℃.
- 3>. Storage Temperature: -40 ℃ to+85℃.
- 4>. Mechanical life: 3000 cycles operations.
- 5>. Resistance to Soldering: 260 ±5℃ for 3-5 Seconds.

2.PLATING:


- 1>. GOLD flash 1u" (min) SOLDERTAIL,
- 3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>. Non-switch Rating:100mA at 50V DC.
- 2>. Switching Rating: 25mA at 24V DC.
- 3>. Contact Resistance: Initial 50mΩ Max. Contact Resistance: After life 100mΩ Max.
- 4>. Insulation Resistance:1000MΩ Min at500VDC.
- 5>. Dielectric Strength: 500V AC for 60seconds.
- 6>. Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSPV XX L S G E T



5.PACKAGE: 57pcs/Tube, 2280pcs/Box.

Drawing	dengkg	Date	2012. 03. 25	LINER	ANGLES	PRODUCT Family	DSPV Series Pitch 2.54mm
Check	zhong	Scale	4:1	>0±0.05	>0° ±0.5°	PRAT NO.	DSPV03LSGET
Approved		Unit	MM	>1±0.10	>5° ±1.0°	FILE NO.	KE-DSPV-003-S-A
Size	A4	Rev.	A	>10±0.30		PROJECTION	

东莞市康深电子科技有限公司
Kongshen Electronics technology co., LTD.