



ROHS compliant



NOTES:

1.Specification:

- 1>. Operation force: 1000gf Max.
- 2>. Operation Temperature: -30℃ to +85℃.
- 3>. Storage Temperature: -40℃ to +85℃.
- 4>. Mechanical life: 3000 cycles operations.
- 5>. Resistance to Soldering: 260±5℃ for 3-5 Seconds.

2.PLATING:



- 1>. GOLD flash 1u" (min) SOLDER TAIL, 3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>. Non-switch Rating: 100mA at 50V DC.
- 2>. Switching Rating: 25mA at 24V DC.
- 3>. Contact Resistance: Initial 50mΩ Max. Contact Resistance: After life 100mΩ Max.
- 4>. Insulation Resistance: 1000MΩ Min at 500VDC.
- 5>. Dielectric Strength: 500V AC for 60seconds.
- 6>. Switch Capacitance: 5pF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSIC XX T S G E T



5.PACKING: 22pcs/Tube, 1760pcs/Box.

[P. C. B. LAYOUT]

[Schematic]

Drawing	dengkg	Date	2018.03.24	LINER	ANGLES	PRODUCT Family	DSIC Series	Pitch 2.54mm
Check	zhong	Scale	4:1			PRAT NO.	DSIC09LSGET	
Approved		Unit	MM			FILE NO.	KE-DSIC-009-S-A	
Size	A4	Rev.	A			PROJECTION		

东莞市康深电子科技有限公司
Kongshen Electronics technology co., LTD.