



ROHS compliant



NOTES:

1.Specification:

- 1>. Operation force: 1000gf Max.
- 2>. Operation Temperature: -30 ℃ to+85℃.
- 3>. Storage Temperature: -40 ℃ to+85℃.
- 4>. Mechanical life: 3000 cycles operations.
- 5>. Resistance to Soldering: 260 ±5℃ for 3-5 Seconds.

2.PLATING:


- 1>. GOLD flash 1u" (min) SOLDERTAIL, 3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:


- 1>. Non-switch Rating:100mA at 50V DC.
- 2>. Switching Rating: 25mA at 24V DC.
- 3>. Contact Resistance: Initial 50mΩ Max. Contact Resistance: After life 100mΩ Max.
- 4>. Insulation Resistance:1000MΩ Min at500VDC.
- 5>. Dielectric Strength: 500V AC for 60seconds.
- 6>. Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSIC XX T S G E T



5.PACKING: 16pcs/Tube, 800pcs/Box.



[P. C. B. LAYOUT]

[Schematic]

Drawing	dengkg	Date	2018.03.24	LINER	ANGLES	PRODUCT Family DSIC Series Pitch 2.54mm	
	Check	zhong	Scale	4:1		PRAT NO.	DSIC12LHGT
	Approved		Unit	MM		FILE NO.	KE-DSIC-012-H-A
Size	A4	Rev.	A			PROJECTION	

东莞市康深电子科技有限公司
Kongshen Electronics technology co., LTD.