

P-Channel Enhancement Mode MOSFET



Description:

This P-Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.

Features:

- 1) $V_{DS}=-40V, I_D=-65A, R_{DS(on)}<11m\Omega @V_{GS}=-10V$
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 5) Excellent package for good heat dissipation.



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
DMP4015SK3Q	P4015	TO- 252	2500 pcs/Reel

Absolute Maximum Ratings: ($T_C=25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	-40	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current	-65	A
	Continuous Drain Current- $T_C=100^{\circ}C$	-44.8	
I_{DM}	Pulsed Drain Current ¹	-252	
P_D	Power Dissipation	79	W
E_{AS}	Single pulse avalanche energy ²	272	mJ
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55-+175	$^{\circ}C$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.9	$^{\circ}C/W$

Electrical Characteristics: (T_C=25 °C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	-40	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =-40V	---	---	-1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} = ± 20V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	GATE-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	-1	-1.7	-2.5	V
R _{DS(ON)}	Drain-Source On Resistance	V _{GS} =-10V, I _D =-15A	---	9	11	m Ω
		V _{GS} =-4.5V, I _D =-10A	---	13.5	17.5	m Ω
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =-20V, V _{GS} =0V, f=1MHz	---	3403	---	pF
C _{oss}	Output Capacitance		---	229	--	
C _{rss}	Reverse Transfer Capacitance		---	169	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DS} =-20V, R _{ENG} =3 Ω ,V _{GS} =-10V	---	11.4	---	ns
t _r	Rise Time		---	13.4	---	ns
t _{d(off)}	Turn-Off Delay Time		---	38	---	ns
t _f	Fall Time		---	12	---	ns
Q _g	Total Gate Charge	V _{GS} =-10V, V _{DS} =-20V, I _D =-20A	---	60	---	nc
Q _{gs}	Gate-Source Charge		---	8.6	---	nc
Q _{gd}	Gate-Drain “Miller” Charge		---	15.2	---	nc
Drain-Source Diode Characteristics						
V _{SD}	Diode Forward Voltage ³	V _{GS} =0V, I _{SD} =-15A	---	---	-1.2	V
I _S	Continuous Drain Curren	VD=VG=0V	---	---	-65	A
I _{SM}	Pulsed Drain Current		---	---	-252	A
T _{rr}	Reverse Recovery Time	I _F =-20A, T _J =25 °C	---	43	---	ns
Q _{rr}	Reverse Recovery Charge	dI/dt=100A/us	---	48	---	nc

Notes:

- 1.Repetitive Rating: Pulse width limited by maximum junction temperature.
- 2.EAS condition: $T_J=25^{\circ}\text{C}$, $V_{DD}=40\text{V}$, $V_G=-10\text{V}$, $R_g=25\Omega$, $L=0.5\text{mH}$.
- 3.Repetitive Rating: Pulse width limited by maximum junction temperature.

Typical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)




Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Power Dissipation




Figure 4. Drain Current




Figure 5. BV_{DSS} vs Junction Temperature




Figure 6. $R_{DS(ON)}$ vs Junction Temperature




Figure 7. Gate Charge Waveforms




Figure 8. Capacitance




Figure 9. Body-Diode Characteristics





Figure 10. Maximum Safe Operating Area

TO-252 Package Information


Package Outline Type-A

UNIT: mm



DIM.	MILLIMETER		
	MIN.	NOM.	MAX.
A	2.18	2.30	2.39
A1	0	--	0.13
b	0.64	0.76	0.89
c	0.40	0.50	0.61
c1	0.46	0.50	0.58
D	5.97	6.10	6.23
D1	5.05	--	--
E	6.35	6.60	6.73
E1	4.32	--	--
b3	5.21	5.38	5.55
e	2.29 BSC		
H	9.40	10.00	10.40
L	0.89	--	1.27
L2	1.40	--	1.78
V1	7° REF		
V2	0°	--	6°

Package Outline Type-B



DIM.	MILLIMETER		
	MIN.	NOM.	MAX.
A	2.10	2.30	2.40
A1	0	--	0.13
b	0.66	0.76	0.86
b3	5.21	5.38	5.55
c	0.40	0.50	0.60
c1	0.44	0.50	0.58
D	5.90	6.10	6.30
D1	5.30REF		
E	6.40	6.60	6.80
E1	4.63	-	-
e	2.29 BSC		
H	9.50	10.00	10.70
L	1.09	--	1.21
L2	1.35	--	1.65
V1	7° REF		
V2	0°	--	6°

Recommended Soldering Footprint

