

SCHOTTKY BARRIER DIODE
FEATURES

- ◆ Low Forward Voltage Drop
- ◆ Guard Ring Construction for Transient Protection
- ◆ Negligible Reverse Recovery Time
- ◆ Low Capacitance
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- ◆ Case: SOD-123
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 16mg / 0.00056oz

Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Pinning	
1.Cathode	2.Anode
SOD-123	

Marking Code	
SD103AW	S4
SD103BW	S5
SD103CW	S6

Parameter	Symbols	SD103AW	SD103BW	SD103CW	Units
Peak Repetitive Reverse Voltage	V_{RRM}	40	30	20	V
RMS reverse voltage	V_{RMS}	28	21	14	V
Working Peak Reverse Voltage	V_{DC}	40	30	20	V
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed On Rated Load(JEDEC method)	I_{FSM}		13		A
Maximum Instantaneous Forward Voltage	$I_F=20mA$	V_F	0.37		V
	$I_F=200mA$		0.60		
Power Dissipation	P_D	400			mW
Reverse current	$SD103AW, V_R=30V$	I_R	5	-	-
	$SD103BW, V_R=20V$		-	5	-
	$SD103CW, V_R=10V$		-	-	5
Thermal Resistance, Junction to Ambient Air	$R_{\theta JA}$	300			°C/W
Reverse voltage $I_R=100\mu A$	$SD103AW$	$V_{(BR)R}$	40		
	$SD103BW$		30		
	$SD103CW$		20		
Reverse recovery time $I_F=I_R=200mA, I_{RR}=0.1 \times I_R, RL=100\Omega$	T_{rr}	10			nS
Forward Continuous Current	I_{FM}	350			mA
Total capacitance $V_R=0V, f=1MHz$	C_{tot}	28			pF
Junction temperature	T_j	125			°C
Storage temperature	T_{stg}	-55 ~ +150			°C

Fig.1 Power Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Forward Characteristics




Fig.4 Maximum Non-Repetitive Peak Forward Surge Current




Fig.5 Typical Junction Capacitance






Fig.6 Typical Transient Thermal Impedance



Package Outline


SOD-123

Plastic surface mounted package; 2leads



UNIT		A	C	D	E	E ₁	L ₁	b	A ₁	<
mm	max	1.3	0.22	1.8	2.8	3.9	0.45	0.7	0.2	9°
	min	0.9	0.09	1.5	2.5	3.6	0.25	0.5	—	
mil	max	51	8.7	71	110	154	18	28	8	9°
	min	35	3.5	59	98	142	10	20	—	

The recommended mounting pad size



Unit: $\frac{\text{mm}}{(\text{mil})}$

Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
SOD-123	Tape/Reel,7"reel	3000	EIA-481-1