


■ PRODUCT CHARACTERISTICS

| | |
|--------------------------------------------------|------|
| VDSS | 20V |
| R _{DS(on)} Typ(@V _{GS} =10 V) | 7mΩ |
| R _{DS(on)} Typ(@V _{GS} =4.5 V) | 12mΩ |
| ID | 50A |



■ APPLICATIONS

- * Switching applications

■ FEATURES

- * Low capacitance
- * Low gate charge
- * Fast switching capability
- * Avalanche energy specified



■ ORDER INFORMATION

| Order codes | | Package | Packing |
|--------------|-----------|---------|-------------------|
| Halogen-Free | Halogen | | |
| N/A | MOT50N02D | TO-252 | 2500 pieces /Reel |
| N/A | MOT50N02C | TO-251 | 70 pieces/Tube |

■ ORDER INFORMATION

| PARAMETER | SYMBOL | RATINGS | UNIT |
|-------------------------------------|------------------|------------|------|
| Drain-Source Voltage | V _{DSS} | 20 | V |
| Gate-Source Voltage | V _{GSS} | ±12 | V |
| Continuous Drain Current | I _D | 50 | A |
| Pulsed Drain Current | I _{DM} | 90 | A |
| Avalanche Current | I _{AR} | 30 | A |
| Repetitive avalanche energy L=0.1mH | E _{AR} | 135 | mJ |
| Power Dissipation | P _D | 50 | W |
| Junction Temperature | T _J | +175 | °C |
| Storage Temperature | T _{STG} | -55 ~ +175 | °C |

Note: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Pulse width limited by T_{J(MAX)}






■ THERMAL DATA

| PARAMETER | SYMBOL | RATINGS | UNIT |
|---------------------|-----------------|---------|------|
| Junction-to-Ambient | θ _{JA} | 50 | °C/W |
| Junction-to-Case | θ _{JC} | 3 | °C/W |


■ ELECTRICAL CHARACTERISTICS ($T_c=25^\circ\text{C}$, unless otherwise specified)

| PARAMETER | SYMBOL | TEST CONDITIONS | MIN | TYP | MAX | UNIT | |
|-----------------------------------|----------------------------|----------------------------------------------------------------------------------|-------------------------------------------------------------------------------|------|------|------------------|-------------|
| OFF CHARACTERISTICS | | | | | | | |
| Drain-Source Breakdown Voltage | BV_{DSS} | $V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$ | 20 | - | - | V | |
| Drain-Source Leakage Current | I_{DSS} | $V_{\text{DS}}=20\text{V}, V_{\text{GS}}=0\text{V}$ | - | - | 1 | μA | |
| Gate-Source Leakage Current | I_{GSS} | $V_{\text{DS}}=0\text{V}, V_{\text{GS}}=\pm 12\text{V}$ | - | - | 100 | nA | |
| ON CHARACTERISTICS | | | | | | | |
| Gate Threshold Voltage | $V_{\text{GS}(\text{TH})}$ | $V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$ | 0.4 | 0.7 | 1.1 | V | |
| On State Drain Current | $I_{\text{D}(\text{ON})}$ | $V_{\text{DS}}=5\text{V}, V_{\text{GS}}=10\text{V}$ | 100 | - | - | A | |
| Static Drain-Source On-Resistance | $R_{\text{DS}(\text{ON})}$ | $V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}$ | - | 7 | 8 | $\text{m}\Omega$ | |
| | | $V_{\text{GS}}=4.5\text{V}, I_{\text{D}}=20\text{A}$ | - | 12 | 13 | | |
| Forward Transconductance | g_{FS} | $V_{\text{DS}}=5\text{V}, I_{\text{D}}=10\text{A}$ | - | 35 | - | S | |
| DYNAMIC PARAMETERS | | | | | | | |
| Input Capacitance | C_{ISS} | $V_{\text{DS}}=10\text{V}, V_{\text{GS}}=0\text{V}, f=1\text{MHz}$ | - | 1230 | - | pF | |
| Output Capacitance | C_{OSS} | | - | 315 | - | pF | |
| Reverse Transfer Capacitance | C_{RSS} | | - | 190 | - | pF | |
| SWITCHING PARAMETERS | | | | | | | |
| Total Gate Charge | 10V | Q_G | $V_{\text{DS}}=10\text{V}, V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}$ | - | 26.4 | - | nC |
| | 4.5V | | | - | 13.5 | - | |
| Gate Source Charge | | Q_{GS} | | - | 3.9 | - | nC |
| Gate Drain Charge | | Q_{GD} | | - | 7.75 | - | nC |
| Turn-ON Delay Time | $t_{\text{D}(\text{ON})}$ | $V_{\text{GS}}=10\text{V}, V_{\text{DS}}=10\text{V}, R_L=0.6\Omega, R_G=3\Omega$ | $R_L=0.6\Omega, R_G=3\Omega$ | - | 6.5 | - | ns |
| Turn-ON Rise Time | t_R | | | - | 10 | - | ns |
| Turn-OFF Delay Time | $t_{\text{D}(\text{OFF})}$ | | | - | 22.7 | - | ns |
| Turn-OFF Fall-Time | t_F | | | - | 6.2 | - | ns |

■ TYPICAL CHARACTERISTICS



■ TO-251 PACKAGE OUTLINE DIMENSIONS



■ TO-252 PACKAGE OUTLINE DIMENSIONS

